




SFC-120-T2-L-D-A



SFC-110-T1-L-D-A



SFC-135-T2-L-D-A-K



(1.27 mm) .050"

SFC SERIES

COST-EFFECTIVE RELIABLE SOCKET

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ " (1.27 μ m) Ni

Current Rating:

3.1 A per pin

(2 pins powered)

Voltage Rating:

350 VAC mated with TFC

Operating Temp Range:

-55 °C to +125 °C

Insertion Depth:

(3.05 mm) .120" to

(4.06 mm) .160"

Max Cycles:

10,000 with 30 μ " (0.76 μ m) Au

RoHS Compliant:

Yes

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (04-25)

(0.15 mm) .006" max (30-50)*

*(.004" stencil solution may be available)

RECOGNITIONS


Board Mates:
TFC

Cable Mates:
TFSD, TFSDT



**TIGER
EYE**
LITE

High-reliability
Tiger Eye™ LITE
contacts



(1.27 mm x 1.27 mm)
.050" x .050"
micro pitch

Slotted SMT tails

Alignment pin option

Polarized

SFC

1

NO. PINS
PER ROWLEAD
STYLEPLATING
OPTION

D

OPTION

04, 05, 10,
15, 20, 25, 30,
35, 40, 45, 50
(Standard sizes)

—T1
= Through-hole
Tiger Eye™ LITE

—T2
= Surface Mount
Tiger Eye™ LITE

—F
= Gold flash on contact,
Matte Tin on tail

—L
= 10 μ " (0.25 μ m)
Gold on contact,
Matte Tin on tail




—A
= Alignment Pin

—K
= (4.00 mm) .157" DIA
Polyimide film
Pick & Place Pad

—TR
= Tape & Reel
(-T2 only)

ALSO AVAILABLE (MOQ Required)

- Other sizes



Note: Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.TOBY.CO.UK

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.