



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RLSD; NPR NSD07-105	18JAN2008	GG	SJ
	B	REV PER ECO-14-004513	09APR2014	JB	MS




SUGGESTED MOUNTING PATTERN

- ALL DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
- POWER STRIP IS WIRED PER ELECTRICAL SCHEMATIC.
- MATERIAL:
JUNCTION BOX HOUSINGS - POLYCARBONATE, UL 94V-0, BLACK.
JUNCTION BOX DUST COVER - 6/6, UL 94V-0 RATED.
JUNCTION BOX CONTACTS - COPPER ALLOY SELECTIVELY TIN-PLATED AND SILVER PLATED 0.00508 [0.000200] MINIMUM THICKNESS.
POWER STRIP BRACKET - ZINC PLATED CARBON STEEL.
- APPLICATION:
AMPINNERGY - MODULAR POWER DISTRIBUTION SYSTEM, A MANUFACTURED WIRING SYSTEM.
THE POWER STRIP IS DESIGNED TO BE MOUNTED USING THE KEYHOLE PATTERN IN THE MOUNTING BRACKET WITH CUSTOMER SUPPLIED FASTENERS, 4 PLACES.

	BLANK	BLANK	9-1933414-9
OBsolete	LINE 3G	LINE 3	7-1933414-3
OBsolete	LINE 3G	LINE 2	7-1933414-2
OBsolete	LINE 3G	LINE 1	7-1933414-1
OBsolete	LINE 2G	LINE 3	6-1933414-3
OBsolete	LINE 2G	LINE 2	6-1933414-2
OBsolete	LINE 2G	LINE 1	6-1933414-1
OBsolete	LINE 1G	LINE 3	5-1933414-3
OBsolete	LINE 1G	LINE 2	5-1933414-2
OBsolete	LINE 1G	LINE 1	5-1933414-1
	LINE 2	LINE 3	2-1933414-3
	LINE 1	LINE 3	1-1933414-3
	LINE 1	LINE 2	1-1933414-2
OBsolete	LINE 3G	LINE 3G	1933414-7
OBsolete	LINE 2G	LINE 2G	1933414-6
OBsolete	LINE 1G	LINE 1G	1933414-5
	LINE 3	LINE 3	1933414-3
	LINE 2	LINE 2	1933414-2
	LINE 1	LINE 1	1933414-1
	LEFT SIDE LINE NUMBER	RIGHT SIDE LINE NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT CHK S. JONES APVD S. JONES	18JAN2008 18JAN2008 18JAN2008	TE Connectivity	
DIMENSIONS: MME[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±" 1 PLC ±" 2 PLC ±" 3 PLC ±" 4 PLC ±" ANGLES ±" FINISH ±"		PRODUCT SPEC 108-1234 APPLICATION SPEC 114-6039 WEIGHT CUSTOMER DRAWING	
MATERIAL 3		SIZE A1		CAGE CODE 1933414	
		SCALE 1:1		SHEET 1 OF 3	
				REV B	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
--		SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 18JAN2008	TE Connectivity	
DIMENSIONS: MME[INCHES]		CHK S. JONES 18JAN2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. JONES 18JAN2008	NAME POWER STRIP, KEYHOLE MOUNT, 2 PORT, 3-3-2	
0 PLC ±"		PRODUCT SPEC	SIZE A1	
1 PLC ±"		108-1234	CAGE CODE -	
2 PLC ±"		APPLICATION SPEC	DRAWING NO 1933414	
3 PLC ±"		114-6039	RESTRICTED TO -	
4 PLC ±"		WEIGHT -	REV B	
ANGLES FINISH		CUSTOMER DRAWING		
MATERIAL -		SCALE 1:1		
-		SHEET 2 OF 3		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
--		SEE SHEET 1	-	-	-

BLANK	BLANK/BLANK	BLANK/BLANK	BLANK	BLANK	BLANK/BLANK	BLANK/BLANK	BLANK	9-1933414-9
ISOLATED	N3/4	3G/8	15/20	STANDARD	N3/4	L3/8	15/20	7-1933414-3
ISOLATED	N3/4	3G/8	15/20	STANDARD	N2/3	L2/7	15/20	7-1933414-2
ISOLATED	N3/4	3G/8	15/20	STANDARD	N1/2	L1/6	15/20	7-1933414-1
ISOLATED	N2/3	2G/7	15/20	STANDARD	N3/4	L3/8	15/20	6-1933414-3
ISOLATED	N2/3	2G/7	15/20	STANDARD	N2/3	L2/7	15/20	6-1933414-2
ISOLATED	N2/3	2G/7	15/20	STANDARD	N1/2	L1/6	15/20	6-1933414-1
ISOLATED	N1/2	1G/6	15/20	STANDARD	N3/4	L3/8	15/20	5-1933414-3
ISOLATED	N1/2	1G/6	15/20	STANDARD	N2/3	L2/7	15/20	5-1933414-2
ISOLATED	N1/2	1G/6	15/20	STANDARD	N1/2	L1/6	15/20	5-1933414-1
STANDARD	N2/3	L2/7	15/20	STANDARD	N3/4	L3/8	15/20	2-1933414-3
STANDARD	N1/2	L1/6	15/20	STANDARD	N3/4	L3/8	15/20	1-1933414-3
STANDARD	N1/2	L1/6	15/20	STANDARD	N2/3	L2/7	15/20	1-1933414-2
ISOLATED	N3/4	3G/8	15/20	ISOLATED	N3/4	3G/8	15/20	1933414-7
ISOLATED	N2/3	2G/7	15/20	ISOLATED	N2/3	2G/7	15/20	1933414-6
ISOLATED	N1/2	1G/6	15/20	ISOLATED	N1/2	1G/6	15/20	1933414-5
STANDARD	N3/4	L3/8	15/20	STANDARD	N3/4	L3/8	15/20	1933414-3
STANDARD	N2/3	L2/7	15/20	STANDARD	N2/3	L2/7	15/20	1933414-2
STANDARD	N1/2	L1/6	15/20	STANDARD	N1/2	L1/6	15/20	1933414-1
GROUND TYPE	NEUTRAL NO./CONTACT NO.	LINE NO./CONTACT NO.	AMPERAGE	GROUND TYPE	NEUTRAL NO./CONTACT NO.	LINE NO./CONTACT NO.	AMPERAGE	PART NO.
LEFT-SIDE DUPLEX RECEPTACLE CONNECTIONS				RIGHT-SIDE DUPLEX RECEPTACLE CONNECTIONS				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
G. GARRETT
18JAN2008

CHK
S. JONES
18JAN2008


APVD
S. JONES
18JAN2008

TE Connectivity

NAME
POWER STRIP, KEYHOLE MOUNT,
2 PORT, 3-3-2

RESTRICTED TO
-

DIMENSIONS:
MME[INCHES]



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±"
1 PLC ±"
2 PLC ±"
3 PLC ±"
4 PLC ±"
ANGLES ±"
FINISH

PRODUCT SPEC
108-1234

APPLICATION SPEC
114-6039

WEIGHT
-

CUSTOMER DRAWING

SIZE
A1

CAGE CODE
-

DRAWING NO.
1933414

SCALE
1:1

SHEET
3

OF
3

REV
B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1-1933414-3](#)