

# IDXPERT™ Handheld Labeler



**More Options, More Brains,  
More Brawn...Less Waste.**



**Two printer layouts—identical  
functionality and supplies.**

## More Types of Labels

- Colored Continuous tapes for equipment ID and safety warnings
- PermaSleeve™ wire marker sleeves
- Self-Laminating wire & cable markers
- Terminal Block markers
- Patch Panel markers
- Face Plate & Outlet markers
- General-purpose industrial die-cut labels

## More Sizes

- Prints from .06" up to 1.25" characters on label stock up to 1.5" wide

## More Symbols

- Code 39 and 128 bar codes
- 82 Symbols including electrical, voice/data, safety & protection, warning, and machine & operational

## More Brains

- Drop Lock & Go™ Smart Cartridges™ are fast to install and remove
- Electronically pre-calibrated to orient the label just the way you need it with no special keys to press
- Print stand-alone or from a PC (with optional Brady LabelMark™ software)
- Memory to store frequently used set-ups

## Prints Clean & Fast

- Users of dot-matrix printers will benefit from crisp, non-smearing thermal transfer print quality, faster print speed and more text-editing and symbols capabilities


## Less Waste

- Edge-to-edge printing on continuous tapes so you don't pay for unused label material
- Die-cut labels are pre-cut to the size you need—no waste
- Runs on 6 AAs or optional AC power supply

| Catalog No.     | Description                        |
|-----------------|------------------------------------|
| XPRT-ABC        | Printer* (ABC Layout)              |
| XPRT-HC-ABC     | Hard Case for ABC Layout           |
| XPRT-KEY        | Printer* (KEYBOARD Layout)         |
| XPRT-HC-KEY     | Hard Case for KEYBOARD Layout      |
| XPRT-AC         | AC Adapter                         |
| LABXPRT-SER-USB | Serial-to-USB adapter for PC cable |
| PCCABLE-1       | Spare PC Cable for Upgrades Only   |
| PCK-6           | Cleaning Kit                       |
| LM3             | LabelMark™ software (single user)  |

\*Printer ships with: Hard Case, 1.5" Cont. Tape, PC cable  
Product CD

## Diagram



## Indoor/Outdoor Grade Facility & Safety Labels

This indoor/5 year outdoor vinyl is very pliable and conforms well to smooth or rough surfaces such as pipes, walls, doors, panels, shelving, bins and equipment. Aggressive permanent adhesive. Excellent resistance to oils, detergents, dirt, grime and many solvents.

- B-580 Indoor/Outdoor Vinyl material
- Permanent adhesive, good for rough surfaces
- Temp Range -40°F to 248°F (-40C to 120C)

| Diagram | Part Number       | Labels per Cartridge | Dimensions (in.) |       | Dimensions (mm) |        | Color    |
|---------|-------------------|----------------------|------------------|-------|-----------------|--------|----------|
|         |                   |                      | A                | B     | A               | B      |          |
| ⊙       | XC-500-580-WT-BK  | 1 roll (cont.)       | 30 ft.           | 0.500 | 9.14m           | 12.70m | BK on WT |
| ⊙       | XC-1000-580-WT-BK | 1 roll (cont.)       | 30 ft.           | 1.000 | 9.14m           | 25.40m | BK on WT |
| ⊙       | XC-1500-580-WT-BK | 1 roll (cont.)       | 30 ft.           | 1.500 | 9.14m           | 38.10m | BK on WT |
| ⊙       | XC-500-580-OR-BK  | 1 roll (cont.)       | 30 ft.           | 0.500 | 9.14m           | 12.70m | BK on OR |
| ⊙       | XC-1000-580-OR-BK | 1 roll (cont.)       | 30 ft.           | 1.000 | 9.14m           | 25.40m | BK on OR |
| ⊙       | XC-1500-580-OR-BK | 1 roll (cont.)       | 30 ft.           | 1.500 | 9.14m           | 38.10m | BK on OR |
| ⊙       | XC-500-580-YL-BK  | 1 roll (cont.)       | 30 ft.           | 0.500 | 9.14m           | 12.70m | BK on YL |
| ⊙       | XC-1000-580-YL-BK | 1 roll (cont.)       | 30 ft.           | 1.000 | 9.14m           | 25.40m | BK on YL |
| ⊙       | XC-1500-580-YL-BK | 1 roll (cont.)       | 30 ft.           | 1.500 | 9.14m           | 38.10m | BK on YL |
| ⊙       | XC-500-580-CL-BK  | 1 roll (cont.)       | 30 ft.           | 0.500 | 9.14m           | 12.70m | BK on CL |
| ⊙       | XC-1000-580-CL-BK | 1 roll (cont.)       | 30 ft.           | 1.000 | 9.14m           | 25.40m | BK on CL |
| ⊙       | XC-1500-580-CL-BK | 1 roll (cont.)       | 30 ft.           | 1.500 | 9.14m           | 38.10m | BK on CL |
| ⊙       | XC-500-580-RD-WT  | 1 roll (cont.)       | 30 ft.           | 0.500 | 9.14m           | 12.70m | WT on RD |
| ⊙       | XC-1000-580-RD-WT | 1 roll (cont.)       | 30 ft.           | 1.000 | 9.14m           | 25.40m | WT on RD |
| ⊙       | XC-1500-580-RD-WT | 1 roll (cont.)       | 30 ft.           | 1.500 | 9.14m           | 38.10m | WT on RD |
| ⊙       | XC-500-580-GN-WT  | 1 roll (cont.)       | 30 ft.           | 0.500 | 9.14m           | 12.70m | WT on GN |
| ⊙       | XC-1000-580-GN-WT | 1 roll (cont.)       | 30 ft.           | 1.000 | 9.14m           | 25.40m | WT on GN |
| ⊙       | XC-1500-580-GN-WT | 1 roll (cont.)       | 30 ft.           | 1.500 | 9.14m           | 38.10m | WT on GN |
| ⊙       | XC-500-580-BL-WT  | 1 roll (cont.)       | 30 ft.           | 0.500 | 9.14m           | 12.70m | WT on BL |
| ⊙       | XC-1000-580-BL-WT | 1 roll (cont.)       | 30 ft.           | 1.000 | 9.14m           | 25.40m | WT on BL |
| ⊙       | XC-1500-580-BL-WT | 1 roll (cont.)       | 30 ft.           | 1.500 | 9.14m           | 38.10m | WT on BL |
| ⊙       | XC-500-580-WT-RD  | 1 roll (cont.)       | 30 ft.           | 0.500 | 9.14m           | 12.70m | RD on WT |
| ⊙       | XC-1000-580-WT-RD | 1 roll (cont.)       | 30 ft.           | 1.000 | 9.14m           | 25.40m | RD on WT |
| ⊙       | XC-1500-580-WT-RD | 1 roll (cont.)       | 30 ft.           | 1.500 | 9.14m           | 38.10m | RD on WT |