


CONFIGURATION		PART NUMBER	LENGTH
PowerBOSSlite Cable Assembly, Molded, 14Awg, Standard Flex, Connectors Female Straight Entry, Single Ended		P29018-MXX	AS REQUESTED
DIMENSIONS			
			
TECHNICAL DATA			
TEMPERATURE RANGE:	-20C to +90C		
PROTECTION:	IP 67, NEMA 6P		
BODY:	OIL RESISTANT PVC		
CONTACTS:	COPPER ALLOY		
CONTACT PLATING:	GOLD OVER NICKEL PLATING		
CONNECTOR FACE:	PVC BLACK		
AMPERAGE:	15AMP		
COUPLING:	MACHINED ALUMINUM, ANODIZED		
CABLE CHARACTERISTICS:	UL TYPE TC 600V 90°C DRY 75°C WET, EXPOSED RUN (ER) OR MTW 600V 90°C OR STOOW 105°C 600V - CSA STOOW 600V FT2		
APPROVALS:	UL, c(UL)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[P29018-M0.5](#) [P29018-M1](#) [P29018-M1.5](#) [P29018-M2](#) [P29018-M2.5](#) [P29018-M3](#) [P29018-M4](#) [P29018-M5](#) [P29018-M6](#) [P29018-M8](#) [P29018-M10](#) [P29018-M12](#) [P29018-M14](#)