


Plug-in units – for VME

Kits

Plug-in units with trapeziform extractor handle, type 1 – front panel, U-profile, shielded

3 U




- At 6 U the board position can be offset by 1 HP to the right by swapping the top and bottom board supports; thus space is created for SMD components on the left (solder) side; for board thickness 1.6 mm only

Delivery comprises (kit)

Item	Qty	3 U	6 U	Description
1	1	1		Extractor handle, trapeziform type, PPE, grey, bottom
1a	-	1		Extractor handle, trapeziform type, PPE, grey, top
2	1	2		Identification plate, Al, 1.5 mm, anodised, cut edges plain
3	1	2		Pivot bush, Ms
4	1	1		Board support, die-cast zinc, bottom
4a	-	1		Board support, die-cast zinc, top
5	1	-		Board support, die-cast zinc
6	1	1		Front panel, U profile, for trapeziform extractor handle, front anodised, rear conductive
7	2	2		Alignment pin, pressed-in, stainless steel
8	2	2		Sleeve, PA, grey, up to 7 HP front panel width
8	4	4		Sleeve, PA, grey, from 8 HP front panel width
9	2	2		Collar screw, Pozidrive/slot, St, nickel-plated, M2.5 × 12.3, front panel width up to 7 HP
9	4	4		Collar screw, Pozidrive/slot, St, nickel-plated, M2.5 × 12.3, front panel width from 8 HP
11	1	2		Raised countersunk panhead screw, M2.5 × 8
12	1	1		EMC gasket (textile)
13	2	2		Washer, A2.7, DIN 125
14	2	2		Pozidrive flathead screw, St, nickel-plated, M2.5 × 10

04602058

6 U



04602059

Order Information

Width	3 U	6 U
HP	Part no.	Part no.
4	20848-485	20848-492
6	20848-487	20848-494
8	20848-489	20848-496
10	20848-490	20848-497
12	20848-491	20848-498



For further information www.schroff.biz/oneclick
oneClick search code = Part no.