

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0718400192

Status:

Inactive

Description:

2.54mm (.100") Pitch C-Grid® Receptacle, Dual Row, Vertical, Low Profile, High-Temperature, 20 Circuits



Documents:

Drawing (PDF)

General	
Product Family	PCB Receptacles
Series	71840
Application	Board-to-Board, Signal
Product Name	C-Grid®
Physical	
Circuits (Loaded)	20
Durability (mating cycles max)	50
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.49mm (.137")
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Pitch - Mating Interface	2.54mm (.100")
Polarized to PCB	No
Temperature Range - Operating	-40°C to +105°C
Electrical	
Current - Maximum per Contact	2.5A
Material Info	

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

71840Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION