




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC—F005.DWG

REVISIONS			DOC. NO. SPC--F005 * Effective: 7/8/02 * DCP No: 1398					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			ASH	25-10-10	JAG	25-10-10	XXX	02-11-10



0.181 Diameter (4.6)
4 Positions

Notes:

Material : C1008 Steel
Plating : Bright Nickel Chrome (other plating styles are available upon request)
Ring Diameter : 2.3mm
Rib Diameter : 2.3mm

Dimensions : Inches (mm)

Part Number Table

Description	Part Number
Wire Form Fan Guard	MC32651

TOLERANCES:

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:		DATE:		DRAWING TITLE:			
ASH		25-10-10		Wire Form Fan Guard			
CHECKED BY:		DATE:		SIZE	DWG. NO.	ELECTRONIC FILE	REV
JAG		25-10-10		A	MC32651	56P2928	A
APPROVED BY:		DATE:		SCALE:	NTS	U.O.M.: Millimeters	SHEET: 1 OF 1
XXX		02-11-10					