



Rocker Switches

Commercial Controls Division

EATON

Standard Size Sealed Rockette Switches




The rocker switches offer a remarkable silicone rubber seal that protects contacts and mechanisms better than conventional seal and boot combinations. The switches resist contaminants such as sand, dust and moisture with both base to frame seal and an actuator seal. **Rated:** 15 A, 125 VAC; 10 A, 250 VAC. **Spade Terminals:** Brass. Concave rocker. Illuminated versions available.

Stock No.	Mfr.'s Type*	Circuit	Action (Momentary)	EACH		
				1-24	25-49	50-99
757-5520	8055K23Z7V	SPST	On-None-Off	7.88	6.24	6.02
757-5521	8055K20Z7V	SPDT	On-Off-On	9.06	7.16	6.92
757-5525	8055K43Z7V	DPST	On-None-Off	10.06	8.12	7.83
757-5522	8055K40Z7V	DPDT	On-Off-On (On)-Off-(On)	11.43	9.04	8.73
757-5523	8055K52Z7V	DPDT	On-Off-On	12.91	10.42	10.06

*Other terminations available.

Full Size New Generation Rockers



This all new line of rockers offers European styling, ergonomic design with the solid durability you've come to expect from Eaton switches. Rockers and bezels for the NGR series are molded in a soft matte finish. Illuminated and non-illuminated versions are available.

Non-Illuminated (Rated: 15 A @ 125 VAC, 10 A @ 250 VAC, 15 A @ 28 VDC)

Stock No.	Mfr.'s Type	Circuit	Action (Momentary)	EACH		
				1-24	25-49	50-99
757-5539	NGR20011BN00N	DPST	On-None-Off	8.14	6.44	6.21
757-5540	NGR20031BN00N	DPDT	On-None-Off	11.10	8.79	8.47
757-5541	NGR20041BN00N	DPDT	On-Off-On	9.41	7.45	7.18
757-5542	NGR20051BN00N	DPDT	On-(On)-Off-(On)	11.30	8.95	8.62

Illuminated (Rated: 15 A @ 125 VAC, 10 A @ 250 VAC, 15 A @ 28 VDC)

Stock No.	Mfr.'s Type	Circuit	Action (Momentary)	EACH		
				1-24	25-49	50-99
757-5543	NCR25011BNA0N	DPST	On-None-Off	12.09	9.76	9.40
757-5544	NCR25481BNAAN	DPDT	On-None-On	13.92	11.24	10.83
757-5545	NCR23681BNAAN	DPDT	On-Off-On	13.92	11.24	10.83
757-5546	NCR25881BNAAN	DPDT	On-(On)-Off-(On)	14.08	11.36	10.95


NGR Rocker Button (Ordered Separately; Does Not Include Lens)

Stock No.	Mfr.'s Type	Fig.	Description	EACH		
				1-24	25-49	50-99
757-5567	1B	A	Black Rocker, No Lens	1.60	1.26	1.20
757-5568	2C00050000500	B	Lens Hole Top/Bottom	2.27	1.85	1.79
757-5569	2A000500	C	Lens Hole Top	1.63	1.28	1.23
757-5570	2B000500	D	Lens Hole Bottom	1.63	1.28	1.23

NGR Rocker Lens (Ordered Separately)

Stock No.	Mfr.'s Type	Color	EACH			
			1-24	25-49	50-99	
757-5551	28-5863	Green	.30	.23	.22	
757-5552	28-5863-3	Amber	.30	.23	.22	
757-5553	28-5863-2	Red	.30	.23	.22	

Midsize Snap In AC Rocker Switches



Minimum Panel Thickness — .030 (.075)
Maximum Panel Thickness — .118 (.300)

Panel Cutout

Recommended panel cutout for types 400, 403, 410, 420, 423, 427, 433, 898

Panel Cutout

Recommended panel cutout for types 601, 603, 610, 613, 620, 622, 623, 633

Panel Cutout

Panel Cutout