



LAPP CY

LAPP CY cables are number coded control and connection cables with tinned copper braid screen. EMC compliant and space saving installation due to small cable diameters suitable for flexible use and fixed installation.

LAPP CY cables are suitable for flexible use and fixed installation for medium mechanical use. They are for use in dry, damp and wet rooms. They may only be installed outdoors with UV protection and in observation of the temperature range generally resistant against acids, caustics solutions and certain oils. LAPP CY cables are used as supply and interconnecting cable for controlling machine tools, production lines, control equipment on conveyors, also for use in measuring regulating and computer units. Suitable for free movement without forced guidance and tensile stress.

Typical applications:

Measurement and control technology, office machines and systems for data processing.

Technical data

Conductor	: Bare copper, fine wire strand in accordance to IEC 60 228 that is VDE 0295, class 5.
Core insulation	: PVC compound T11 in accordance to VDE 0207.
Identification	: In acc. to VDE 0293, black cores with white numbers with or without green/yellow ground conductor.
Braid	: Tinned copper wire braid.
Outer sheath	: Grey PVC compound TM2 in acc. to VDE 0207 Grey RAL 7001.
Nominal voltage	: 300 / 500 V
Test voltage	: 3,000 V ac
Temperature range	: For flexible use -5 up to +70°C maximum conductor temperature. Fixed installation -40 up to +80°C maximum conductor temperature.
Minimum bending radius	: Fixed installation 12.5 × cable diameter.
Flame retardant	: In acc. to IEC 60 332.1 resp. VDE 0472 part 804.
EC directive	: This cable confirms to ECD 73 / 23 / EEC (low voltage directive).

Specification Table

Description	Number Cores x Cross Sectional Area (mm ²)	Outer Diameter (mm)	Weight Kg / Km	Part Number
Cable, CY, 3 Core, 0.5 mm, 50M	Lapp CY 3G0.5	6.1	59	PPCY3C0.50 50M
Cable, CY, 4 Core, 0.5 mm, 50M	Lapp CY 4G0.5	6.5	71	PPCY4C0.50 50M
Cable, CY, 5 Core, 0.5 mm, 50M	Lapp CY 5G0.5	7	86	PPCY5C0.50 50M
Cable, CY, 7 Core, 0.5 mm, 50M	Lapp CY 7G0.5	7.5	105	PPCY7C0.50 50M
Cable, CY, 3 Core, 0.75 mm, 50M	Lapp CY 18G0.5	6.5	68.7	PPCY3C0.75 50M
Cable, CY, 4 Core, 0.75 mm, 50M	Lapp CY 4G0.75	7	85.5	PPCY4C0.75 50M
Cable, CY, 5 Core, 0.75 mm, 50M	Lapp CY 5G0.75	7.7	102.4	PPCY5C0.75 50M
Cable, CY, 7 Core, 0.75 mm, 50M	Lapp CY 7G0.75	8.3	127.4	PPCY7C0.75 50M
Cable, CY, 3 Core, 1 mm, 50M	Lapp CY 3G1	6.8	81.6	PPCY3C1.00 50M
Cable, CY, 4 Core, 1 mm, 50M	Lapp CY 4G1	7.3	96.9	PPCY4C1.00 50M
Cable, CY, 5 Core, 1 mm, 50M	Lapp CY 5G1	8.1	122	PPCY5C1.00 50M
Cable, CY, 7 Core, 1 mm, 50M	Lapp CY 7G1	8.8	146.8	PPCY7C1.00 50M
Cable, CY, 3 Core, 1.5 mm, 50M	Lapp CY 3G1.5	7.5	100.4	PPCY3C1.50 50M
Cable, CY, 4 Core, 1.5 mm, 50M	Lapp CY 4G1.5	8.2	129.8	PPCY4C1.50 50M
Cable, CY, 5 Core, 1.5 mm, 50M	Lapp CY 5G1.5	8.9	152.7	PPCY5C1.50 50M
Cable, CY, 7 Core, 1.5 mm, 50M	Lapp CY 7G1.5	9.9	196.4	PPCY7C1.50 50M
Cable, CY, 3 Core, 2.5 mm, 50M	Lapp CY 3G2.5	8.9	147.4	PPCY3C2.50 50M
Cable, CY, 4 Core, 2.5 mm, 50M	Lapp CY 4G2.5	9.9	189.8	PPCY4C2.50 50M
Cable, CY, 5 Core, 2.5 mm, 50M	Lapp CY 5G2.5	11	230.9	PPCY5C2.50 50M
Cable, CY, 7 Core, 2.5 mm, 50M	Lapp CY 7G2.5	11.9	291.5	PPCY7C2.50 50M
Cable, CY, 12 Core, 0.5 mm, 50M	Lapp CY 12G0.5	9.9	104	PPCY12C0.50 50M
Cable, CY, 18 Core, 0.5 mm, 50M	Lapp CY 18G0.5	11.5	141	PPCY18C0.50 50M
Cable, CY, 12 Core, 0.75 mm, 50M	Lapp CY 12G0.75	10.9	232	PPCY12C0.75 50M
Cable, CY, 18 Core, 0.75 mm, 50M	Lapp CY 18G0.75	12.7	211	PPCY18C0.75 50M
Cable, CY, 12 Core, 1 mm, 50M	Lapp CY 12G1	11.5	285	PPCY12C1.00 50M
Cable, CY, 18 Core, 1 mm, 50M	Lapp CY 18G1	13.9	395	PPCY18C1.00 50M
Cable, CY, 12 Core, 1.5 mm, 50M	Lapp CY 12G1.5	13	332	PPCY12C1.50 50M
Cable, CY, 18 Core, 1.5 mm, 50M	Lapp CY 18G1.5	15.6	553	PPCY18C1.50 50M
Cable, CY, 12 Core, 2.5 mm, 50M	Lapp CY 12G2.5	16	589	PPCY12C2.50 50M
Cable, CY, 18 Core, 2.5 mm, 50M	Lapp CY 18G2.5	19	978	PPCY18C2.50 50M

Specification Table

Description	Number Cores x Cross Sectional Area (mm ²)	Outer Diameter (mm)	Weight Kg / Km	Part Number
Cable, CY, 3 Core, 0.5 mm, Per M	Lapp CY 3G0.5	6.1	59	PPCY3C0.50
Cable, CY, 3 Core, 0.75 mm, Per M	Lapp CY 18G0.5	6.5	68.7	PPCY3C0.75
Cable, CY, 3 Core, 1 mm, Per M	Lapp CY 3G1	6.8	81.6	PPCY3C1.00
Cable, CY, 3 Core, 1.5 mm, Per M	Lapp CY 3G1.5	7.5	100.4	PPCY3C1.50
Cable, CY, 3 Core, 2.5 mm, Per M	Lapp CY 3G2.5	8.9	147.4	PPCY3C2.50
Cable, CY, 4 Core, 0.5 mm, Per M	Lapp CY 4G0.5	6.5	71	PPCY4C0.50
Cable, CY, 4 Core, 0.75 mm, Per M	Lapp CY 4G0.75	7	85.5	PPCY4C0.75
Cable, CY, 4 Core, 1 mm, Per M	Lapp CY 4G1	7.3	96.9	PPCY4C1.00
Cable, CY, 4 Core, 1.5 mm, Per M	Lapp CY 4G1.5	8.2	129.8	PPCY4C1.50
Cable, CY, 4 Core, 2.5 mm, Per M	Lapp CY 4G2.5	9.9	189.8	PPCY4C2.50
Cable, CY, 5 Core, 0.5 mm, Per M	Lapp CY 5G0.5	7	86	PPCY5C0.50
Cable, CY, 5 Core, 0.75 mm, Per M	Lapp CY 5G0.75	7.7	102.4	PPCY5C0.75
Cable, CY, 5 Core, 1 mm, Per M	Lapp CY 5G1	8.1	122	PPCY5C1.00
Cable, CY, 5 Core, 1.5 mm, Per M	Lapp CY 5G1.5	8.9	152.7	PPCY5C1.50
Cable, CY, 5 Core, 2.5 mm, Per M	Lapp CY 5G2.5	11	230.9	PPCY5C2.50
Cable, CY, 7 Core, 0.5 mm, Per M	Lapp CY 7G0.5	7.5	105	PPCY7C0.50
Cable, CY, 7 Core, 0.75 mm, Per M	Lapp CY 7G0.75	8.3	127.4	PPCY7C0.75
Cable, CY, 7 Core, 1 mm, Per M	Lapp CY 7G1	8.8	146.8	PPCY7C1.00
Cable, CY, 7 Core, 1.5 mm, Per M	Lapp CY 7G1.5	9.9	196.4	PPCY7C1.50
Cable, CY, 7 Core, 2.5 mm, Per M	Lapp CY 7G2.5	11.9	291.5	PPCY7C2.50
Cable, CY, 12 Core, 0.5 mm, Per M	Lapp CY 12G0.5	9.9	104	PPCY12C0.50
Cable, CY, 12 Core, 0.75 mm, Per M	Lapp CY 12G0.75	10.9	232	PPCY12C0.75
Cable, CY, 12 Core, 1 mm, Per M	Lapp CY 12G1	11.5	285	PPCY12C1.00
Cable, CY, 12 Core, 1.5 mm, Per M	Lapp CY 12G1.5	13	332	PPCY12C1.50
Cable, CY, 12 Core, 2.5 mm, Per M	Lapp CY 12G2.5	16	589	PPCY12C2.50
Cable, CY, 18 Core, 0.5 mm, Per M	Lapp CY 18G0.5	11.5	141	PPCY18C0.50
Cable, CY, 18 Core, 0.75 mm, Per M	Lapp CY 18G0.75	12.7	211	PPCY18C0.75
Cable, CY, 18 Core, 1 mm, Per M	Lapp CY 18G1	13.9	395	PPCY18C1.00
Cable, CY, 18 Core, 1.5 mm, Per M	Lapp CY 18G1.5	15.6	553	PPCY18C1.50
Cable, CY, 18 Core, 2.5 mm, Per M	Lapp CY 18G2.5	19	978	PPCY18C2.50

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or Personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2011.