



Engineer Grade Prismatic Reflective Sheeting

Series 3430 with Pressure Sensitive Adhesive

Product Bulletin 3430-U.S.

October 2013

Replaces Product Bulletin 3430 dated July 2009

Description

3M™ Engineer Grade Prismatic Reflective Sheeting Series 3430 is a non-metalized microprismatic lens retroreflective sheeting designed for production of reflective commercial signs and noncritical traffic control signs that are exposed vertically in service. Series 3430 sheeting can easily be identified by the visible integral “EGP” marking. When applied to properly prepared sign substrates, Series 3430 sheeting provides long-term reflectivity and durability. Series 3430 sheeting is available in the following colors.

Color	Product Code
White	3430
Yellow	3431
Red	3432
Blue	3435
Green	3437
Brown	3439

Sign Fabrication Methods

Application

Series 3430 sheeting incorporates a pressure sensitive adhesive and should be applied to the sign substrate at temperature of 65°F/18°C or higher by any of the following methods:

Mechanical squeeze roll applicator – Reference Information Folder 1.4.

Hand squeeze roll applicator — Reference Information Folder 1.6.

Hand application is recommended for copy only. See Information Folder 1.5.

All direct applied copy and border MUST be cut at all panel seams and squeegeed at the joint.

Splices

Series 3430 sheeting must be butt spliced when more than one piece of sheeting is used on one piece of substrate. The sheeting pieces should not touch each other. This is to prevent buckling as the sheeting expands when subject to extreme temperature and/or high humidity levels.

Double Faced Signs

The sheeting on the bottom side of a double faced sign can be damaged if rolled through a squeeze roll applicator with an unprotected steel bottom roller. The use of a semi-soft flat sheet between the steel roller and the applied sign face will provide protection from damage. A material such as a rubber mat, tag board or cardboard is recommended.

Substrates	For traffic sign use, substrates found to be most reliable and durable are properly prepared aluminum sheets and extrusions. Users are urged to carefully evaluate all other substrates for adhesion and sign durability. Other substrates that may be satisfactory for proper application of sheeting will have the following characteristics: • Clean • Smooth • Flat • Rigid • Dimensionally stable • Weather resistant • Non-porous • High surface energy (passes water break test) Refer to Information Folder 1.7 for surface preparation recommendations. Substrates with low surface energy may require additional preparation such as flame treatment, mechanical abrasion or use of adhesion promoters prior to sheeting application. Engineer grade prismatic sheeting is designed primarily for applications to flat substrates. Any use that requires a radius of curvature of less than five inches should also be supported by rivets or bolts. Plastic substrates are not recommended where cold shock performance is required. Sign failures caused by the substrate or improper surface preparation are not the responsibility of 3M.
Screen Processing	Engineer grade prismatic sheeting may be screen processed into traffic signs before or after mounting on a sign substrate, using 3M™ Process Colors Series 880I or Series 880N. Series 880I or 880N process colors can be screened at 60–100°F (16–38°C) at relative humidity of 20–50%. A PE 157 screen mesh with a fill pass is recommended. Refer to Information Folder 1.8 for details. Clear coating is not required or recommended. Use of other process colors series is not recommended. Care should be taken to avoid flexing series 3430 sheeting before and especially after screening to eliminate the possibility of cracking from improper handling techniques. For screenprinted areas on white sheeting when processed according to 3M recommendations, the coefficients of retroreflection shall not be less than 70% of the value for the corresponding color in Table A. The color chromaticity and luminance shall conform to Table B.
Cutting and Matching	Engineer grade prismatic sheeting may be cut into letters and shapes of at least three inches in height and stroke widths of at least one half inch. Smaller sizes are not recommended. Sealing cut edges of Series 3430 sheeting is not required. Plotter Cutting Programmable knife cut (electronic cutting) 1. Flat bed plotters can either die cut or kiss cut and offer the most consistent and reliable performance. 2. Friction fed plotter. Kiss cut only. Success has been achieved using plotters that have 600 grams of down force and a 60° cutting blade. Additional drive wheels may need to be added to improve tracking. An alternative procedure is to cut sheeting from the liner side. Blade force and knife depth must be set to score but not cut through the topfilm. Break apart individual copy or apply premask to retain spacing. Other Cutting Methods Engineer grade prismatic sheeting may be hand cut or die cut one sheet at a time, and band sawed or guillotined in stacks. Cutting equipment such as guillotines and metal shears, which have pressure plates on the sheeting when cutting, may damage the optics. Padding the pressure plate and easing it down onto the sheets being cut will significantly reduce damage. Maximum stack height for cutting series 3430 sheeting is one and a half inch or 50 sheets. Details on cutting can be found in Information Folder 1.10.

Cleaning	Signs that require cleaning should be flushed with water, then washed with a detergent solution and a soft bristle brush or sponge. Avoid pressure that may damage the sign face. Flush with water following washing. Do not use solvents to clean signs. See Information Folder 1.10.
Storage and Packaging	3M™ Engineer Grade Prismatic Sheeting should be stored in a cool, dry area, preferably at 65–75°F (18–24°C) and 30–50% relative humidity and should be applied within one year of purchase. Rolls should be stored horizontally in the shipping carton. Partially used rolls should be returned to the shipping carton or suspended horizontally from a rod or pipe through the core. Unprocessed sheets should be stored flat. Finished signs and applied blanks should be stored on edge. Screen processed signs must be protected with SCW 568 slipsheet paper. Place the glossy side of the slipsheet against the sign face. Double faced signs must have the glossy side of the slipsheet against each face of the sign. Unmounted screened faces must be stored flat and interleaved with SCW 568 slipsheet, glossy side against the sign face. Avoid banding, crating, or stacking signs. Package for shipment in accordance with commercially accepted standards to prevent movement and chafing. Store sign packages indoors on edges. Panels or finished signs must remain dry during shipment and storage. If packaged signs become wet, unpack immediately and allow signs to dry. Refer to Information Folder 1.11 for instructions on packing for storage and shipment.
Installation	Nylon washers are required when twist style fasteners are used to mount the sign.
Health and Safety Information	Read all health hazard, precautionary and first aid statements found in the Material Safety Data Sheet, and/or product label of chemicals prior to handling or use.
General Performance Considerations	Minimum coefficient of retroreflection, chromaticity limits, and daytime luminance factor (Y%) for the engineer grade prismatic sheeting series 3430 are given in Table A and Table B, respectively. Durability Considerations The durability of 3M™ Engineer Grade Prismatic Sheeting and finished signs using 3M's matched component materials (Table C) will depend upon substrate selection and preparation, compliance with recommended application procedures, geographic area, exposure conditions, and maintenance. Maximum durability of series 3430 can be expected in applications subject to vertical exposure on stationary objects when processed and applied to properly prepared aluminum according to 3M recommendations. Periodic sign inspection and regular sign replacement are strongly recommended in order for sign owners to establish their own effective service life expectation beyond any durability warranty, if provided. Substrate Considerations The user must determine the suitability of any nonmetallic sign backing for its intended use. Substrate manufacturer recommendations for preparation should be followed as well as guidance provided in Information Folder 1.7. Applications to unprimed, excessively rough or non-weather resistant surfaces can shorten the performance of such applications. Sign failures caused by the substrate or improper surface preparation are not the responsibility of 3M. Exposure Considerations Exposure to severe or unusual conditions can shorten the performance of such applications. Signs in mountainous areas that are covered by snow for prolonged periods may also have reduced durability. Atmospheric conditions in certain geographic areas may result in reduced durability. Custom Process Colors Considerations Custom colors, certain lighter colors, heavily toned color or blends containing yellow or gold may have reduced durability.

General Performance Considerations (Continued)

Table A — Minimum Coefficient of Retroreflection
Candelas/Foot Candle/Square Foot
Candelas/Lux/Square Meter

Obs. Angle ¹	Ent. Angle ²	White	Yellow	Red	Green	Blue	Brown
0.2	-4	70	50	14.5	9.0	4.0	2.0
0.2	+30	30	22	6.0	3.5	1.7	1.0
0.5	-4	30	25	7.5	4.5	2.0	1.0
0.5	+30	15	13	3.0	2.2	0.8	0.5

Reflectivity conforms to ASTM D 4956.

¹Observation Angle — The angle between the illumination axis and the observation axis.

²Entrance Angle — The angle from the illumination axis to the retroreflector axis. The retroreflector axis is an axis perpendicular to the retroreflective surface.

Table B — CIE Chromaticity Coordinate Limits

Color	x	y	x	y	x	y	x	y	Reflectance Limit (Y)	
									Min	Max
White	.303	.300	.368	.366	.340	.393	.274	.329	27.0	
Yellow	.498	.412	.557	.442	.479	.520	.438	.472	15.0	45.0
Red	.648	.351	.735	.265	.629	.281	.565	.346	2.5	12.0
Blue	.140	.035	.244	.210	.190	.255	.065	.216	1.0	10.0
Green	.026	.399	.166	.364	.286	.446	.207	.771	3.5	9.0
Brown	.430	.340	.610	.390	.550	.450	.430	.390	4.0	9.0

Table C — Matched Component Materials

Matched Components	
Process Colors	Series 880I
Process Colors	Series 880N
Premium Protective Overlay Film	Series 1160
Slipsheet	SCW 568
Prespacing Tape	SCPS-2
Premasking Tape	SCPM-3
Transfer Tape	TPM-5

3M Basic Warranty and Limited Remedy

3M™ Engineer Grade Prismatic Reflective Sheeting Series 3430 (“Product”) is warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in this Product Bulletin. If the product is proven not to have met the Basic Warranty on its shipment date, then a buyer’s exclusive remedy, and 3M’s sole obligation, at 3M’s option, will be refund or replacement of the sheeting.

Limitation of Liability and Remedies

3M WILL NOT UNDER ANY CIRCUMSTANCES BE LIABLE TO A BUYER FOR DIRECT (other than the applicable Limited Remedy stated above), SPECIAL, INCIDENTAL, INDIRECT OR CONSEQUENTIAL DAMAGES (INCLUDING, WITHOUT LIMITATION, LOSS OF PROFITS) IN ANY WAY RELATED TO A PRODUCT OR THIS PRODUCT BULLETIN, REGARDLESS OF THE LEGAL OR EQUITABLE THEORY ON WHICH SUCH DAMAGES ARE SOUGHT.

Literature Reference	Information Folder 1.4	Instructions for Squeeze Roll Applicator
	Product Bulletin 880I	3M™ Process Color Series 880I
	Product Bulletin 880N	3M™ Process Color Series 880N
	Information Folder 1.5	Hand Application Instructions
	Information Folder 1.6	Instructions for Hand Squeeze Roll Applicator
	Information Folder 1.7	Sign Base Surface Preparation
	Information Folder 1.8	Process Color Instructions
	Information Folder 1.10	Cutting, Matching, Premasking, and Prespacing Instructions
	Information Folder 1.11	Sign Maintenance Management

**FOR INFORMATION OR ASSISTANCE
CALL: 1-800-553-1380**

**IN CANADA CALL:
1-800-265-1840**

**Internet:
www.3M.com/roadwaysafety**

3M assumes no responsibility for any injury, loss or damage arising out of the use of a product that is not of our manufacture. Where reference is made in literature to a commercially available product, made by another manufacturer, it shall be the user's responsibility to ascertain the precautionary measures for its use outlined by the manufacturer.

Important Notice

All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed, and the following is made in lieu of all warranties, or conditions express or implied. Seller's and manufacturer's only obligation shall be to replace such quantity of the product proved to be defective. Neither seller nor manufacturer shall be liable for any injury, loss or damage, direct, special or consequential, arising out of the use of or the inability to use the product. Before using, user shall determine the suitability of the product for his/her intended use, and user assumes all risk and liability whatsoever in connection therewith. Statements or recommendations not contained herein shall have no force or effect unless in an agreement signed by officers of seller and manufacturer.

3M is a trademark of 3M. Used under license in Canada.



Traffic Safety and Security Division
3M Center, Building 0235-3A-09
St. Paul, MN 55144-1000
1-800-553-1380
www.3M.com/roadwaysafety

3M Canada Company
P.O. Box 5757
London, Ontario N6A 4T1

3M México, S.A. de C.V.
Av. Santa Fe No. 55
Col. Santa Fe, Del. Alvaro Obregón
México, D.F. 01210

Please recycle.
© 3M 2013. All rights reserved.