



# Product Catalog

for professionals

[Products](#) > 66132

## 66132 – LED7DMR16/827/35

GE LED MR16

**This product is no longer manufactured. Remaining stock is on Firesale.**

- Energy-efficient LED lamps. Long life.



UL damp rated

### GENERAL CHARACTERISTICS

Lamp type	Replacement Lamps - Directional
Bulb	MR16
Base	2-Pin (GU5.3)
ENERGY STAR® Qualified	Yes
Primary Application	Indoor Floodlight
Additional Info	GE Life Rating is based on 70% Lumen Maintenance
Bulb Shape	MR16
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	35 W
Lamp Type	LED-MR
Life in Years (NOM)	23
Rated Life (NOM)	25000 hrs

### PHOTOMETRIC CHARACTERISTICS

Beam Spread (NOM)	35.0 °
Center Beam Candlepower (CBCP) (NOM)	1100
Color Rendering Index (CRI) (NOM)	84
Color Temperature (NOM)	2700 K
Initial Lumens (NOM)	370
Lumens per Watt (Efficacy) (NOM)	53 lm
Nominal Initial Lumens per Watt (NOM)	53

### ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year (NOM)	0.84
Voltage (NOM)	12.0
Wattage (NOM)	7.0

### DIMENSIONS

Bulb Diameter (DIA) (NOM)	2.0000 in (50.8 mm)
Maximum Overall Length (MOL) (NOM)	1.8800 in (47.7 mm)

### PRODUCT INFORMATION

Product Code	66132
Description	LED7DMR16/827/35
Standard Package	Case

Standard Package GTIN	10043168661321
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	1
UPC	043168661324

**⚠ CAUTIONS & WARNINGS**

---