





LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	CI	REVISED PER ECO-12-007964	02MAY2012	KH	MS	



- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.
- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC.FILE N° E60677.
- 4 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 5 NOT CUMULATIVE TOLERANCE.




282816-2 AS SHOWN



125	13	1-282816-3
115	12	1-282816-2
105	11	1-282816-1
95	10	1-282816-0
85	9	282816-9
75	8	282816-8
65	7	282816-7
55	6	282816-6
45	5	282816-5
35	4	282816-4
25	3	282816-3
15	2	282816-2
DIM. A		N° OF POS. PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.2
1 PLC ±.2
2 PLC ±.25
3 PLC ±.
4 PLC ±.
ANGLES ±2

MATERIAL

FINISH

DWN
E. ZANOLINI
CHK
D. BIEVENOUR
APVD
D. BIEVENOUR

25JUL2001
25JUL2001
25JUL2001

PRODUCT SPEC
108-20166
APPLICATION SPEC
114-20079
WEIGHT
-

NAME
TERMINAL BLOCK HEADER ASSEMBLY
90 DEGREE CLOSED ENDS
10mm PITCH

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-282816

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE 3:1

SHEET 1 OF 1

REV C1