

Part Number: 1301450066

Status: Active Overview: Heavy-Duty Industrial Wiring Devices

Description: Super-Safeway® Receptacle with Locking Blade, 3 Pole/3 Wire, Non-NEMA, 250V

Documents:

Note - Please disable browser pop-up blockers for documents on www.molex.com

[RoHS Certificate of Compliance \(PDF\)](#)



EU RoHS  
ELV and RoHS Compliant

China RoHS

REACH SVHC  
Not Reviewed



Low-Halogen Status  
Not Reviewed

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130145](#)Series

Part Detail: [\(show all\)](#)

General Physical Electrical Agency Certification Material Info

General

|                    |                                      |
|--------------------|--------------------------------------|
| Product Family     | Wiring Devices                       |
| Series             | 130145                               |
| IP Rating          | N/A                                  |
| NEMA Configuration | Non-NEMA Locking                     |
| Overview           | Heavy-Duty Industrial Wiring Devices |
| Product Name       | Super-Safeway™                       |
| Receptacle Type    | Single                               |
| Specialty          | N/A                                  |
| Type               | Connector                            |

Physical

|                     |               |
|---------------------|---------------|
| Cord Grip Body Size | N/A           |
| Flange              | No            |
| Flip Lid            | No            |
| Gender              | Receptacle    |
| Length              | N/A           |
| Locking Blade       | Yes           |
| Poles               | 3-pole/3-wire |

Electrical(Please review the Product Specification for specific details.)

|                               |      |
|-------------------------------|------|
| Cord Type                     | N/A  |
| Current - Maximum per Contact | 30A  |
| GFCI                          | No   |
| Lighted Connector             | No   |
| Voltage - Maximum             | 250V |

Agency Certification

|     |        |
|-----|--------|
| CSA | LR6837 |
| UL  | E10176 |

Material Info

|                 |      |
|-----------------|------|
| Old Part Number | 2908 |
|-----------------|------|