



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
G	14		F	REV PER ECR 10-000722	22JAN10	JR TM



AMP WIRE RANGE	Listed FILE E13288
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
2/0 AWG SOLID OR STRANDED	MS 20659-153 CLASS 2

- 1 STAMP AMP 2/OW* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 TIN PLATE 0/00254 [.000100] MIN EXT THK PER ASTM B-545

50	LOOSE PIECE	321869
QTY	PACKAGE TYPE	PART NO.
Tyco Electronics Corporation Harrisburg, PA 17105-3608		
NAME TERMINAL, RING TONGUE, SOLISTRAND		
SIZE	CAGE CODE	DRAWING NO
A2	00779	C=321869
RESTRICTED TO	SCALE	SHEET
-	2:1	1 of 1
REV	F	

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 1/14/94
	DIMENSIONS: MM [INCHES]		CHK AJ KAUFMAN 1/19/94
VOLTAGE RATING: N/A		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD JL MECKLEY 1/19/94
			PRODUCT SPEC —
CIRCULAR MIL AREA: 60.6–76.3mm ² [119,500–150,500] SOLID OR STRANDED	MATERIAL - 	FINISH - 	APPLICATION SPEC —
			WEIGHT —
			CUSTOMER DRAWING