



NEUTRIK

NYS322G



DIN male cable connector, 5-pole, gold plated contacts

Product

Connector Type	DIN
Gender	male

Electrical

Contact resistance	< 10 mΩ
Dielectric strength	0,5 kVdc
Rated current per contact	depends on mated connector A

Mechanical

Cable O.D.	≤ 5 mm
Wire size	26 AWG

Material

Bushing	PVC
Contact plating	0.2 μm Au
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6 30 % GR)
Shell	Zinc diecast (ZnAl4Cu1), gal Ni plated
Strain relief	CRIMP type zn plated

Environmental

Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +70 °C