

You are here: [Products](#) » [Heatsinks f.cool](#) » [Profile heatsinks and fluid coolers](#) » [Standard extruded heatsinks](#) » [SK 79 ...](#) » [SK 79](#)



▼ Heatsinks f.cool

- ▼ Profile heatsinks and fluid coolers
 - [Standard extruded heatsinks](#)
 - Extruded heatsinks for lock-in retaining spring
 - Extruded heatsinks for PCB mounting
 - Extruded heatsinks for DC/DC converter
 - Retaining springs for transistors
 - U-Extruded heatsinks
 - Die-cast heatsinks
 - Fin coolers
 - Fluid coolers
 - Aluminium flat-, quadrangular-, angled-, U- and T-profiles
- Heatsinks and active heatsinks for processors
- Board Level heatsinks
- Cooling aggregates
- Accessories for electronic components

► Cases f.case

► Connectors f.con

Standard extruded heatsinks

SK 79 ...

SK 79 50 SA

88 x 25 mm, with guide away for cover plates or blanks

Data sheet

add to request



Features

Technical Drawing

Service

thermal resistance R_{θ}	3 - 1.75 K/W
drilling pattern	TO 3 CB
surface	black anodised
height	25 mm
width B	88 mm
length	50 mm
plate thickness	4.5 mm