




AMP

63.5

[2.500]

REF

6.27

[.247]

REF

6.35

TYP.

[.250]

4.98

[.196]

REF

SCALE 5:1

1.09

[.043]

REF

5.08

[.200]

REF

2.44

[.096]

BREAK HERE

SECTION C-C

SCALE 15:1

CONTACT AREA

CONTACT

HOUSING

CARRIER STRIP

SCALE 2:1

ISOMETRIC VIEW

SECTION A-A

SCALE 15:1

2.54

[.100]

1. MATERIAL:

HOUSING: GLASS-FILLED POLYESTER

CONTACT: PHOSPHOR BRONZE

2. CONNECTOR MATES WITH 0.64 [0.025] SQUARE POSTS.

3. PART DENOTES INDIVIDUAL TWO POSITION SHUNT WHICH IS PACKAGED ON BREAKAWAY COMBS OF TEN SHUNTS.

4

 ASSEMBLIES ARE DELIVERED IN STICKS OF TEN PARTS.

5

 FINISH: 1.27μm [0.00050] MIN NICKEL UNDERPLATE OVERALL.

6

 FINISH: 0.76μm [0.00030] MIN GOLD IN CONTACT AREA.

7

 FINISH: 0.38μm [0.00015] MIN GOLD IN CONTACT AREA.

COLOR	SIZE	PART NUMBER	NOTES
YELLOW	15AU	390088-6	4 5 7
YELLOW	30AU	390088-5	4 5 6
BLUE	15AU	390088-4	4 5 7
BLUE	30AU	390088-3	4 5 6
BLACK	15AU	390088-2	4 5 7
BLACK	30AU	390088-1	4 5 6

DWN

CHK

APVD

PPS

22-Sep-99

14-NOV-97

14-NOV-97

TE Connectivity

SHUNT, DUAL BEAM

.100 CL

SIZE

CAGE CODE

DRAWING NO

A2

00779

390088

CUSTOMER DRAWING

SCALE

SHEET

OF

REV

A3

Pro/ENGINEER DRAWING