

Strain Relief

Dustight Strain Relief Grips

Aluminum Fittings, Galvanized Steel Mesh, for Insulated Cables

**Non-Insulated** Wide Range Strain Relief

Cable Diameter Range Inches (cm.)	Thread Size N.P.T. (Inches)	Mesh Length @ Nom. Dia. Inches (cm)	Catalog Numbers
.24"-.32" (.61-.81)	1/2"	3 1/4" (8.25)	073031200
.32"-.43" (.81-1.09)	1/2"	3 3/4" (9.52)	073031201
.43"-.54" (1.09-1.37)	1/2"	4 3/4" (12.06)	073031202
.54"-.73" (1.37-1.85)	3/4"	6 1/2" (16.51)	073031203
.73"-.97" (1.85-2.46)	1"	7" (17.78)	073031204
.97"-1.25" (2.46-3.17)	1 1/4"	9" (22.86)	073031205
.73"-.97" (1.85-2.46)	PG29	7" (17.78)	073PG291204

Insulated Wide Range Strain Relief with Insulating Bushing

Cable Diameter Range In. (cm.)	Thread Size Inches	Mesh Length @ Nom. Dia. Inches (cm)	Dim. A In. (cm)	Min. Space Between Grips B In. (cm)	Catalog Numbers
.24"-.32" (.61-.81)	1/2" N.P.S.	3 1/4" (8.25)	1" (2.54)	1 1/4" (3.17)	073031206
.32"-.43" (.81-1.09)	1/2" N.P.S.	3 3/4" (9.52)	1" (2.54)	1 1/4" (3.17)	073031207
.43"-.54" (1.09-1.37)	1/2" N.P.S.	4 3/4" (12.06)	1" (2.54)	1 1/4" (3.17)	073031208
.54"-.73" (1.37-1.85)	3/4" N.P.S.	6 1/2" (16.51)	1" (2.54)	1 1/2" (3.81)	073031209
.73"-.97" (1.85-2.46)	1" N.P.S.	7" (17.78)	1 3/16" (3.02)	1 3/4" (4.44)	073031210
.97"-1.25" (2.46-3.17)	1 1/4" N.P.S.	9" (22.86)	1 3/16" (3.02)	2 1/4" (5.71)	073031211
1.25"-1.50" (3.17-3.81)	1 1/2" N.P.T.	11 3/4" (29.84)	1 3/16" (3.02)	2 1/2" (6.35)	073031212
1.50"-1.70" (3.81-4.32)	2" N.P.T.	13 1/4" (33.65)	1 3/8" (3.49)	3 1/4" (8.25)	073031213
1.70"-2.00" (4.32-5.08)	2 1/2" N.P.T.	13 1/2" (34.29)	1 1/2" (3.81)	3 5/8" (9.21)	073031214
2.00"-2.45" (5.08-6.22)	2 1/2" N.P.T.	13 3/4" (34.92)	1 1/2" (3.81)	3 5/8" (9.21)	073031215

Read This Data

It is important that you read all breaking strength, safety and technical data relating to this product on pages T-68 through T-74.

**Non-Insulated****Insulated**