



Sample photo

Order symbol: ABS 150/60 HG
Product nbr: 6081313
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074022936
EL. number:
Finland 3420551
Denmark 8212023262
Italy 7361090
Sweden 2535751

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Rating:
	L	W	H
mm:	180	130	60
inch:	7.1	5.1	2.4
Materials:			
Material:	ABS		
Gasket material:	TPE		
Base colour:	RAL 7035		
Cover colour:	RAL 7035		
Cover screws material:	Polyamide		
Cover screws colour:	Grey		
Temperatures:			
Short term:	-40 ... 80 °C		
Continuous:	-40 ... 60 °C		
Short term:	-40 ... 175 °F		
Continuous:	-40 ... 140 °F		
Accessories:			
MIV 150	Mounting plate (Galvanized steel)		
MIN 10	DIN-15 Mounting rail		
MIN 15	DIN-15 Mounting rail		
MIV 10	DIN-35 Mounting rail		
MIV 15	DIN-35 Mounting rail		
FP A 150/180	Front plate (Aluminium)		
HFP 180	Front plate hinge series (2 pcs)		
FP 22046	Wall fastening lug (4 pcs)		
Electrical insulation: Totally insulated			
Halogen free (DIN/VDE 0472, Part 815): Yes			
Flammability Rating (UL 746 C 5): UL 94 HB			
Glow Wire Test (IEC 695-2-1) °C: 650			
NEMA Class: NEMA 1, 4, 4X, 6			
Ingress Protection (EN 60529): IP 66/67			
Impact Resistance (EN 50102): IK 07			
Certificates:			
Fimko			
Europe EN 50298: 1998			
Gost R			

