



# DS1230Y/AB

## 256k Nonvolatile SRAM

www.maxim-ic.com


### FEATURES

- 10 years minimum data retention in the absence of external power
- Data is automatically protected during power loss
- Replaces 32k x 8 volatile static RAM, EEPROM or Flash memory
- Unlimited write cycles
- Low-power CMOS
- Read and write access times of 70 ns
- Lithium energy source is electrically disconnected to retain freshness until power is applied for the first time
- Full  $\pm 10\%$   $V_{CC}$  operating range (DS1230Y)
- Optional  $\pm 5\%$   $V_{CC}$  operating range (DS1230AB)
- Optional industrial temperature range of  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ , designated IND
- JEDEC standard 28-pin DIP package
- PowerCap Module (PCM) package
  - Directly surface-mountable module
  - Replaceable snap-on PowerCap provides lithium backup battery
  - Standardized pinout for all nonvolatile SRAM products
  - Detachment feature on PowerCap allows easy removal using a regular screwdriver

### PIN ASSIGNMENT

|     |    |    |                  |
|-----|----|----|------------------|
| A14 | 1  | 28 | $V_{CC}$         |
| A12 | 2  | 27 | $\overline{WE}$  |
| A7  | 3  | 26 | A13              |
| A6  | 4  | 25 | A8               |
| A5  | 5  | 24 | A9               |
| A4  | 6  | 23 | $\overline{A11}$ |
| A3  | 7  | 22 | $\overline{OE}$  |
| A2  | 8  | 21 | $\overline{A10}$ |
| A1  | 9  | 20 | $\overline{CE}$  |
| A0  | 10 | 19 | DQ7              |
| DQ0 | 11 | 18 | DQ6              |
| DQ1 | 12 | 17 | DQ5              |
| DQ2 | 13 | 16 | DQ4              |
| GND | 14 | 15 | DQ3              |

28-Pin Encapsulated Package  
740-mil Extended



34-Pin PowerCap Module (PCM)  
(Uses DS9034PC+ or DS9034PCI+ PowerCap)

### PIN DESCRIPTION

|                 |                    |
|-----------------|--------------------|
| A0 - A14        | - Address Inputs   |
| DQ0 - DQ7       | - Data In/Data Out |
| $\overline{CE}$ | - Chip Enable      |
| $\overline{WE}$ | - Write Enable     |
| $\overline{OE}$ | - Output Enable    |
| $V_{CC}$        | - Power (+5V)      |
| GND             | - Ground           |
| NC              | - No Connect       |

## DESCRIPTION

The DS1230 256k Nonvolatile SRAMs are 262,144-bit, fully static, nonvolatile SRAMs organized as 32,768 words by 8 bits. Each NV SRAM has a self-contained lithium energy source and control circuitry which constantly monitors  $V_{CC}$  for an out-of-tolerance condition. When such a condition occurs, the lithium energy source is automatically switched on and write protection is unconditionally enabled to prevent data corruption. DIP-package DS1230 devices can be used in place of existing 32k x 8 static RAMs directly conforming to the popular byte-wide 28-pin DIP standard. The DIP devices also match the pinout of 28256 EEPROMs, allowing direct substitution while enhancing performance. DS1230 devices in the Low Profile Module package are specifically designed for surface-mount applications. There is no limit on the number of write cycles that can be executed and no additional support circuitry is required for microprocessor interfacing.

## READ MODE

The DS1230 devices execute a read cycle whenever  $\overline{WE}$  (Write Enable) is inactive (high) and  $\overline{CE}$  (Chip Enable) and  $\overline{OE}$  (Output Enable) are active (low). The unique address specified by the 15 address inputs ( $A_0 - A_{14}$ ) defines which of the 32,768 bytes of data is to be accessed. Valid data will be available to the eight data output drivers within  $t_{ACC}$  (Access Time) after the last address input signal is stable, providing that  $\overline{CE}$  and  $\overline{OE}$  (Output Enable) access times are also satisfied. If  $\overline{OE}$  and  $\overline{CE}$  access times are not satisfied, then data access must be measured from the later-occurring signal ( $\overline{CE}$  or  $\overline{OE}$ ) and the limiting parameter is either  $t_{CO}$  for  $\overline{CE}$  or  $t_{OE}$  for  $\overline{OE}$  rather than address access.

## WRITE MODE

The DS1230 devices execute a write cycle whenever the  $\overline{WE}$  and  $\overline{CE}$  signals are active (low) after address inputs are stable. The later-occurring falling edge of  $\overline{CE}$  or  $\overline{WE}$  will determine the start of the write cycle. The write cycle is terminated by the earlier rising edge of  $\overline{CE}$  or  $\overline{WE}$ . All address inputs must be kept valid throughout the write cycle.  $\overline{WE}$  must return to the high state for a minimum recovery time ( $t_{WR}$ ) before another cycle can be initiated. The  $\overline{OE}$  control signal should be kept inactive (high) during write cycles to avoid bus contention. However, if the output drivers are enabled ( $\overline{CE}$  and  $\overline{OE}$  active) then  $\overline{WE}$  will disable the outputs in  $t_{ODW}$  from its falling edge.

## DATA RETENTION MODE

The DS1230AB provides full functional capability for  $V_{CC}$  greater than 4.75 volts and write protects by 4.5 volts. The DS1230Y provides full functional capability for  $V_{CC}$  greater than 4.5 volts and write protects by 4.25 volts. Data is maintained in the absence of  $V_{CC}$  without any additional support circuitry. The nonvolatile static RAMs constantly monitor  $V_{CC}$ . Should the supply voltage decay, the NV SRAMs automatically write protect themselves, all inputs become “don’t care,” and all outputs become high-impedance. As  $V_{CC}$  falls below approximately 3.0 volts, a power switching circuit connects the lithium energy source to RAM to retain data. During power-up, when  $V_{CC}$  rises above approximately 3.0 volts the power switching circuit connects external  $V_{CC}$  to RAM and disconnects the lithium energy source. Normal RAM operation can resume after  $V_{CC}$  exceeds 4.75 volts for the DS1230AB and 4.5 volts for the DS1230Y.

## FRESHNESS SEAL

Each DS1230 device is shipped from Maxim with its lithium energy source disconnected, guaranteeing full energy capacity. When  $V_{CC}$  is first applied at a level greater than 4.25 volts, the lithium energy source is enabled for battery back-up operation.

---

## PACKAGES

The DS1230 devices are available in two packages: 28-pin DIP and 34-pin PowerCap Module (PCM). The 28-pin DIP integrates a lithium battery, an SRAM memory and a nonvolatile control function into a single package with a JEDEC-standard, 600-mil DIP pinout. The 34-pin PowerCap Module integrates SRAM memory and nonvolatile control along with contacts for connection to the lithium battery in the DS9034PC PowerCap. The PowerCap Module package design allows a DS1230 PCM device to be surface mounted without subjecting its lithium backup battery to destructive high-temperature reflow soldering. After a DS1230 PCM is reflow soldered, a DS9034PC PowerCap is snapped on top of the PCM to form a complete Nonvolatile SRAM module. The DS9034PC is keyed to prevent improper attachment. DS1230 PowerCap Modules and DS9034PC PowerCaps are ordered separately and shipped in separate containers. See the DS9034PC data sheet for further information.

**ABSOLUTE MAXIMUM RATINGS**

|                                                  |                 |
|--------------------------------------------------|-----------------|
| Voltage on Any Pin Relative to Ground            | -0.3V to +6.0V  |
| Operating Temperature Range                      |                 |
| Commercial:                                      | 0°C to +70°C    |
| Industrial:                                      | -40°C to +85°C  |
| Storage Temperature Range                        |                 |
| EDIP                                             | -40°C to +85°C  |
| PowerCap                                         | -55°C to +125°C |
| Lead Temperature (soldering, 10s)                | +260°C          |
| <b>Note:</b> EDIP is wave or hand soldered only. |                 |
| Soldering Temperature (reflow, PowerCap)         | +260°C          |

*This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operation sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.*

**RECOMMENDED DC OPERATING CONDITIONS**(T<sub>A</sub>: See Note 10)

| PARAMETER                     | SYMBOL          | MIN  | TYP | MAX             | UNITS | NOTES |
|-------------------------------|-----------------|------|-----|-----------------|-------|-------|
| DS1230AB Power Supply Voltage | V <sub>CC</sub> | 4.75 | 5.0 | 5.25            | V     |       |
| DS1230Y Power Supply Voltage  | V <sub>CC</sub> | 4.5  | 5.0 | 5.5             | V     |       |
| Logic 1                       | V <sub>IH</sub> | 2.2  |     | V <sub>CC</sub> | V     |       |
| Logic 0                       | V <sub>IL</sub> | 0.0  |     | 0.8             | V     |       |

**DC ELECTRICAL CHARACTERISTICS**(V<sub>CC</sub> = 5V ±5% for DS1230AB)(T<sub>A</sub>: See Note 10) (V<sub>CC</sub> = 5V ±10% for DS1230Y)

| PARAMETER                                                   | SYMBOL            | MIN  | TYP  | MAX  | UNITS | NOTES |
|-------------------------------------------------------------|-------------------|------|------|------|-------|-------|
| Input Leakage Current                                       | I <sub>IL</sub>   | -1.0 |      | +1.0 | μA    |       |
| I/O Leakage Current $\overline{CE} \geq V_{IH} \leq V_{CC}$ | I <sub>IO</sub>   | -1.0 |      | +1.0 | μA    |       |
| Output Current @ 2.4V                                       | I <sub>OH</sub>   | -1.0 |      |      | mA    |       |
| Output Current @ 0.4V                                       | I <sub>OL</sub>   | 2.0  |      |      | mA    |       |
| Standby Current $\overline{CE} = 2.2V$                      | I <sub>CCS1</sub> |      | 200  | 600  | μA    |       |
| Standby Current $\overline{CE} = V_{CC} - 0.5V$             | I <sub>CCS2</sub> |      | 50   | 150  | μA    |       |
| Operating Current                                           | I <sub>CCO1</sub> |      |      | 85   | mA    |       |
| Write Protection Voltage (DS1230AB)                         | V <sub>TP</sub>   | 4.50 | 4.62 | 4.75 | V     |       |
| Write Protection Voltage (DS1230Y)                          | V <sub>TP</sub>   | 4.25 | 4.37 | 4.5  | V     |       |


**CAPACITANCE**(T<sub>A</sub> = +25°C)

| PARAMETER                | SYMBOL           | MIN | TYP | MAX | UNITS | NOTES |
|--------------------------|------------------|-----|-----|-----|-------|-------|
| Input Capacitance        | C <sub>IN</sub>  |     | 5   | 10  | pF    |       |
| Input/Output Capacitance | C <sub>I/O</sub> |     | 5   | 10  | pF    |       |


**AC ELECTRICAL CHARACTERISTICS**(V<sub>CC</sub> = 5V ±5% for DS1230AB)(T<sub>A</sub>: See Note 10) (V<sub>CC</sub> = 5V ±10% for DS1230Y)

| PARAMETER                                                         | SYMBOL           | DS1230AB-70<br>DS1230Y-70 |     | UNITS | NOTES |
|-------------------------------------------------------------------|------------------|---------------------------|-----|-------|-------|
|                                                                   |                  | MIN                       | MAX |       |       |
| Read Cycle Time                                                   | t <sub>RC</sub>  | 70                        |     | ns    |       |
| Access Time                                                       | t <sub>ACC</sub> |                           | 70  | ns    |       |
| $\overline{\text{OE}}$ to Output Valid                            | t <sub>OE</sub>  |                           | 35  | ns    |       |
| $\overline{\text{CE}}$ to Output Valid                            | t <sub>CO</sub>  |                           | 70  | ns    |       |
| $\overline{\text{OE}}$ or $\overline{\text{CE}}$ to Output Active | t <sub>COE</sub> | 5                         |     | ns    | 5     |
| Output High-Z from Deselection                                    | t <sub>OD</sub>  |                           | 25  | ns    | 5     |
| Output Hold from Address Change                                   | t <sub>OH</sub>  | 5                         |     | ns    |       |
| Write Cycle Time                                                  | t <sub>WC</sub>  | 70                        |     | ns    |       |
| Write Pulse Width                                                 | t <sub>WP</sub>  | 55                        |     | ns    | 3     |
| Address Setup Time                                                | t <sub>AW</sub>  | 0                         |     | ns    |       |
| Write Recovery Time                                               | t <sub>WR1</sub> | 5                         |     | ns    | 12    |
|                                                                   | t <sub>WR2</sub> | 15                        |     |       | 13    |
| Output High-Z from $\overline{\text{WE}}$                         | t <sub>ODW</sub> |                           | 25  | ns    | 5     |
| Output Active from $\overline{\text{WE}}$                         | t <sub>OEW</sub> | 5                         |     | ns    | 5     |
| Data Setup Time                                                   | t <sub>DS</sub>  | 30                        |     | ns    | 4     |
| Data Hold Time                                                    | t <sub>DH1</sub> | 0                         |     | ns    | 12    |
|                                                                   | t <sub>DH2</sub> | 10                        |     |       | 13    |


## READ CYCLE




## WRITE CYCLE 1



## WRITE CYCLE 2



## POWER-DOWN/POWER-UP CONDITION



## POWER-DOWN/POWER-UP TIMING

( $T_A$ : See Note 10)

| PARAMETER                                                            | SYMBOL    | MIN | TYP | MAX | UNITS   | NOTES |
|----------------------------------------------------------------------|-----------|-----|-----|-----|---------|-------|
| $V_{CC}$ Fail Detect to $\overline{CE}$ and $\overline{WE}$ Inactive | $t_{PD}$  |     |     | 1.5 | $\mu s$ | 11    |
| $V_{CC}$ slew from $V_{TP}$ to 0V                                    | $t_F$     | 150 |     |     | $\mu s$ |       |
| $V_{CC}$ slew from 0V to $V_{TP}$                                    | $t_R$     | 150 |     |     | $\mu s$ |       |
| $V_{CC}$ Valid to $\overline{CE}$ and $\overline{WE}$ Inactive       | $t_{PU}$  |     |     | 2   | ms      |       |
| $V_{CC}$ Valid to End of Write Protection                            | $t_{REC}$ |     |     | 125 | ms      |       |

(T<sub>A</sub> = +25°C)

| PARAMETER                    | SYMBOL          | MIN | TYP | MAX | UNITS | NOTES |
|------------------------------|-----------------|-----|-----|-----|-------|-------|
| Expected Data Retention Time | t <sub>DR</sub> | 10  |     |     | years | 9     |

**WARNING:**

Under no circumstance are negative undershoots, of any amplitude, allowed when device is in battery backup mode.

**NOTES:**

1.  $\overline{WE}$  is high for a Read Cycle.
2.  $\overline{OE} = V_{IH}$  or  $V_{IL}$ . If  $\overline{OE} = V_{IH}$  during write cycle, the output buffers remain in a high-impedance state.
3. t<sub>WP</sub> is specified as the logical AND of  $\overline{CE}$  and  $\overline{WE}$ . t<sub>WP</sub> is measured from the latter of  $\overline{CE}$  or  $\overline{WE}$  going low to the earlier of  $\overline{CE}$  or  $\overline{WE}$  going high.
4. t<sub>DH</sub>, t<sub>DS</sub> are measured from the earlier of  $\overline{CE}$  or  $\overline{WE}$  going high.
5. These parameters are sampled with a 5 pF load and are not 100% tested.
6. If the  $\overline{CE}$  low transition occurs simultaneously with or latter than the  $\overline{WE}$  low transition, the output buffers remain in a high-impedance state during this period.
7. If the  $\overline{CE}$  high transition occurs prior to or simultaneously with the  $\overline{WE}$  high transition, the output buffers remain in high-impedance state during this period.
8. If  $\overline{WE}$  is low or the  $\overline{WE}$  low transition occurs prior to or simultaneously with the  $\overline{CE}$  low transition, the output buffers remain in a high-impedance state during this period.
9. Each DS1230 has a built-in switch that disconnects the lithium source until the user first applies V<sub>CC</sub>. The expected t<sub>DR</sub> is defined as accumulative time in the absence of V<sub>CC</sub> starting from the time power is first applied by the user. This parameter is assured by component selection, process control, and design. It is not measured directly during production testing.
10. All AC and DC electrical characteristics are valid over the full operating temperature range. For commercial products, this range is 0°C to 70°C. For industrial products (IND), this range is -40°C to +85°C.
11. In a power-down condition the voltage on any pin may not exceed the voltage on V<sub>CC</sub>.
12. t<sub>WR1</sub> and t<sub>DH1</sub> are measured from  $\overline{WE}$  going high.
13. t<sub>WR2</sub> and t<sub>DH2</sub> are measured from  $\overline{CE}$  going high.
14. DS1230 modules are recognized by Underwriters Laboratories (UL) under file E99151.

**DC TEST CONDITIONS**

Outputs Open

Cycle = 200 ns for operating current

All voltages are referenced to ground

**AC TEST CONDITIONS**

Output Load: 100 pF + 1TTL Gate

Input Pulse Levels: 0 - 3.0V

Timing Measurement Reference Levels

Input: 1.5V

Output: 1.5V

Input pulse Rise and Fall Times: 5 ns

## ORDERING INFORMATION

| PART             | TEMP RANGE     | SUPPLY TOLERANCE | PIN-PACKAGE  | SPEED GRADE (ns) |
|------------------|----------------|------------------|--------------|------------------|
| DS1230AB-70+     | 0°C to +70°C   | 5V $\pm$ 5%      | 28 740 EDIP  | 70               |
| DS1230ABP-70+    | 0°C to +70°C   | 5V $\pm$ 5%      | 34 PowerCap* | 70               |
| DS1230AB-70IND+  | -40°C to +85°C | 5V $\pm$ 5%      | 28 740 EDIP  | 70               |
| DS1230ABP-70IND+ | -40°C to +85°C | 5V $\pm$ 5%      | 34 PowerCap* | 70               |
| DS1230Y-70+      | 0°C to +70°C   | 5V $\pm$ 10%     | 28 740 EDIP  | 70               |
| DS1230YP-70+     | 0°C to +70°C   | 5V $\pm$ 10%     | 34 PowerCap* | 70               |
| DS1230Y-70IND+   | -40°C to +85°C | 5V $\pm$ 10%     | 28 740 EDIP  | 70               |
| DS1230YP-70IND+  | -40°C to +85°C | 5V $\pm$ 10%     | 34 PowerCap* | 70               |

+Denotes a lead(Pb)-free/RoHS-compliant package.

\*DS9034PC+ or DS9034PCI+ (PowerCap) required. Must be ordered separately.

## PACKAGE INFORMATION

For the latest package outline information and land patterns, go to [www.maxim-ic.com/packages](http://www.maxim-ic.com/packages). Note that a “+”, “#”, or “-” in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

| PACKAGE TYPE | PACKAGE CODE | OUTLINE NO.             | LAND PATTERN NO. |
|--------------|--------------|-------------------------|------------------|
| 28 EDIP      | MDT28+3      | <a href="#">21-0245</a> | —                |
| 34 PCAP      | PC2+4        | <a href="#">21-0246</a> | —                |

**REVISION HISTORY**

| <b>REVISION<br/>DATE</b> | <b>DESCRIPTION</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                      | <b>PAGES<br/>CHANGED</b> |
|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|
| 121907                   | Added package information table; removed the DIP module package drawing and dimension table                                                                                                                                                                                                                                                                                                                                                                             | 9, 10                    |
| 11/10                    | Updated the storage information, soldering temperature, and lead temperature information in the <i>Absolute Maximum Ratings</i> section; removed the -85, -100, -120, -150, and -200 MIN/MAX information from the <i>AC Electrical Characteristics</i> table; updated the <i>Ordering Information</i> table (removed -85, -100, -120, -150, and -200 parts and leaded -70 parts); removed the PowerCap module drawings and updated the <i>Package Information</i> table | 1, 4, 5, 9               |