





Dimensions (In.)
(except where noted)



Specifications:

- Primary voltage: 120V 60Hz 19W
- Exciting current, open circuit: 160mA max.
- DC resistance $\pm 15\%$: 57Ω
- Secondary, no load voltage: 17.7VDC
- Loaded voltage: 12VDC @ 800mA
- DC resistance $\pm 20\%$: $.8\Omega$
- Insulation resistance: $100M\Omega$ @ 500VDC
- Dielectric strength: primary-secondary: 1,500VAC for 1 minute
primary-core: 1,500VAC for 1 minute
secondary-core: 500VAC for 1 minute
- Temperature rise: 65°C max. @ rated load



File No. E170147

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

412-112081