

YAV27L2TC38FX

BURNDY® PRODUCTS

YAV27L2TC38FX

YAV27L2TC38FX : CU HYLUG 3/0 FLEX-
3/8X1

ACTIVE

RoHS
compatible[Assistant](#)[Add to Favorites](#)
[✉ Email Datasheet](#)
[🖨 Print Datasheet](#)

FCI Brings You More

[✉ > Contact our sales/technical support](#)
[📄 > Sample request](#)
[€ > Price request](#)

Specifications

[Download document](#)

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Length (Barrel)	Standard		
Size (Wire)	3/0 AWG		
Stud Hole (Size)	3/8 in.		
Stud Hole (Spacing)	1 in.		
Tongue Angle	Straight		
Tongue Width (in)	1.02 in.		
Wire Type	Flexible Copper		
Strip Length (in)	1 in.		
Physical			
Element A Index	13		
Approvals / Certifications			
UL Listed	Yes		
CSA Certified	Yes		
Other Features			
UPC	78181003574		
Keyword	ya		