

ZLR5-30-01-T-RA



ZF5S-10-01-T-WT

(0,50mm) .0197"

ZLR5, ZF5S SERIES

FLAT FLEXIBLE CABLE (FFC) SOCKET

Mates with:
FJH

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/ZLR5

Insulator Material:

Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Sn over 50µ" (1,27µm) Ni

Weld Tab:

Phosphor Bronze

Operating Temp Range:

-55°C to +105°C

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10mm) .004" max

Note: Some sizes, styles and options are non-standard, non-returnable.

ZLR5

NO. OF POSITIONS

LEAD STYLE

PLATING OPTION

RA

OTHER OPTION

-20, -30

(Call Samtec for other sizes.)

-01


= Contacts on Top only

-T


= Matte Tin

-TR

= Tape & Reel



NO. OF POSITIONS	A	B
-20	(19,20) .756	(10,70) .421
-30	(24,20) .953	(15,70) .618



Mates with:
FJH, ZFHF and flex cable with stiffener thickness of (0,30mm) .012"

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/ZF5S

Insulator Material:

Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Sn over 50µ" (1,27µm) Ni

Weld Tab: Phosphor Bronze

Operating Temp Range:

-55°C to +105°C

Current Rating:

1.4 A @ 50°C ambient

(4 contacts powered)

RoHS Compliant: Yes

Processing:

Lead-Free Solderable: Yes

SMT Lead Coplanarity:

(0,10mm) .004" max (10-30)

(0,15mm) .006" max (40-50)

Note: Some sizes, styles and options are non-standard, non-returnable.

ZF5S

NO. OF POSITIONS

LEAD STYLE

PLATING OPTION

WT

OPTION

-10, -15, -20, -25,
-30, -40, -43, -50
(Call Samtec for other sizes.)

-01

= Contact Bottom

-T


= Matte Tin

-WT

= Weld Tab

-TR

= Tape & Reel Packaging



ALSO AVAILABLE

Vertical, Contact Top and other positions available.
Call Samtec.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292 SAMTEC ISRAEL • Tel: 972-3-7526600
SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766 SAMTEC TAIWAN • Tel: 886-2-2735-6109
SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9512 7747 SAMTEC SOUTH AFRICA • Tel: 27 11 452 8112