



B

蝶番  
CONTINUOUS HINGES

平蝶番

裏蝶番

抜き差し  
蝶番段付  
蝶番クリーン  
ヒンジ特装車  
蝶番フリーザー  
ヒンジ特殊  
蝶番トルク  
ヒンジ

ステー

周辺機器  
(B)

MS-20001 長蝶番

米国軍用規格長蝶番(MS規格)  
MILITARY STANDARD CONTINUOUS HINGES

輸入品

MS-20001  
アルミニウム製

## 特 徴 Feature

- アルミ押出し材のため、軽量で強度があります。
- MS規格適合品
- 加工性に優れています。

- Thanks to aluminum extrusion, this is lightweight and large strength.
- Conformity to MS standard.
- Easy machinable.

仕 様 ●材 質：アルミニウム合金押出材  
(軸はステンレス製)用 途 ●表面仕上：アルマイト処理  
●通信機器・測定機器・船舶・車両・小型コンテナ  
などの筐体

納 期 ●標準品・・・納期お問合せください

- 備 考 ●輸入品のため色が異なることがあります。
- 航空機にはMS規格品をご使用ください。
- 軸の抜け止め加工はしていません。蝶番を必要  
な寸法に切断後軸にカシメ等の抜け止め加工  
をしてご使用ください。
- 両端に抜け止め加工を行う場合は、必ず同じ羽  
根で行ってください。異なる羽根で行うと作動  
不良の原因となります。

Specifi- ●Material: Aluminum alloy extrusion.  
cations (Shaft: Stainless steel)



●Finish: Alumite treatment

Specific- ●Cases for aircraft, communication  
use equipment, measuring equipment,  
ships, vehicles and small containers.Remarks ●A color is sometimes different for the imports.  
●The MS (Military Standard) articles  
must be used for the air crafts.

- The hinge is not processed to prevent  
extraction of the shaft. After cutting the  
hinge to size and before use, fix stops,  
etc., on the shaft to prevent its extraction.
- When fixing stops on both ends, always  
fix on the same wing. Fixing on different  
wings may cause faulty operation.

MS-20001-P3

MS-20001-P8

軸はステンレス製です。  
Shaft is made of stainless steel ●長尺商品のため、送料が掛かります。詳細はお問合せください。軽飛行機の内装に軽量で丈夫です。  
Lightweight and durable for light airplane interior.

| 商品番号<br>Product No. | RoHS | CAD | W <sub>1</sub> | W <sub>2</sub> | t          |            | φD <sub>1</sub> | φD <sub>2</sub> |             | R           | 製品質量(g)<br>Mass | コード<br>Code | 単 価<br>Price | 量販価格 Bulk Price |             |
|---------------------|------|-----|----------------|----------------|------------|------------|-----------------|-----------------|-------------|-------------|-----------------|-------------|--------------|-----------------|-------------|
|                     |      |     |                |                | MAX.       | MIN.       |                 | MAX.            | MIN.        |             |                 |             |              | 数量<br>Quantity  | 単価<br>Price |
| MS-20001-P2         |      |     | 1 1/16(27.0)   | 0.135(3.4)     | 0.056(1.4) | 0.044(1.1) | 0.089(2.3)      | 0.187(4.7)      | 0.173(4.4)  | 0.174(4.4)  | 280             | 12446       | 価格はお問合せください  |                 |             |
| MS-20001-P3         |      |     | 1 1/4(31.8)    | 0.135(3.4)     | 0.056(1.4) | 0.044(1.1) | 0.089(2.3)      | 0.187(4.7)      | 0.173(4.4)  | 0.174(4.4)  | 300             | 12447       |              |                 |             |
| MS-20001-P4         |      |     | 1 1/2(38.1)    | 0.135(3.4)     | 0.056(1.4) | 0.044(1.1) | 0.089(2.3)      | 0.187(4.7)      | 0.173(4.4)  | 0.174(4.4)  | 365             | 12448       |              |                 |             |
| MS-20001-P6         |      |     | 2 (50.8)       | 0.135(3.4)     | 0.056(1.4) | 0.044(1.1) | 0.089(2.3)      | 0.187(4.7)      | 0.187(4.7)  | 0.174(4.4)  | 415             | 12450       |              |                 |             |
| MS-20001-P10        |      |     | 2 3/4(69.8)    | 0.135(3.4)     | 0.056(1.4) | 0.044(1.1) | 0.089(2.3)      | 0.187(4.7)      | 0.173(4.4)  | 0.174(4.4)  | 540             | 12453       |              |                 |             |
| MS-20001-P8         |      |     | 2 (50.8)       | 0.200(5.1)     | 0.076(1.9) | 0.064(1.6) | 0.179(4.5)      | 0.318(8.0)      | 0.302(7.7)  | 0.297(7.5)  | 860             | 12451       |              |                 |             |
| MS-20001-P16        |      |     | 3 15/16(100)   | 0.287(7.3)     | 0.210(5.3) | 0.196(5.0) | 0.179(4.5)      | 0.509(12.9)     | 0.491(12.5) | 0.750(19.0) | 3,270           | 12456       |              |                 |             |

単位はインチ・( )内寸法はmmを示します[四捨五入]。 Unit: inches/dimensions in parentheses: mm

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。