


DESCRIPTION: M8 MALE - PANEL MOUNT (FRONT) - SOLDER CUP - 5 POS.



PANEL CUTOUT

NUT

NOTE:

MATERIAL

HOUSING:
CONTACT:
NUT:
SHELL:
O-RING:

PBT UL94V-0, BLACK
BRASS
BRASS
BRASS
NBR, BLACK

FINISH

CONTACT:

GOLD PLATED
OVER 50u" NICKEL
NICKEL PLATED
NICKEL PLATED

ELECTRICAL

RATED CURRENT:

3A

RATED VOLTAGE:

60V

INSULATION RESISTANCE:

100 MOhms MIN.

CONTACT RESISTANCE:

10 MOhms MAX.

WATER PROOF:

IP67

ENVIRONMENT

OPERATION TEMPERATURE:




-40°C TO +85°C

WIRE GAUGE:

24-28 AWG

855-005-103R00Y

1 = GOLD FLASH
4 = 10u" GOLD



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

CHECKED:

DATE:

NorComp

SCALE:

N.T.S.

SHEET

OF

1 1

REV

1

DWG NO.

855-005-103R00Y