






	95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	2-111446-6
	89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	2-111446-5
	70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	2-111446-4
	65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	2-111446-3
	57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	2-111446-2
	52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	2-111446-1
	47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	2-111446-0
	45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	1-111446-9
	39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	1-111446-8
	78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	1-111446-7
	34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16	1-111446-6
	32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	1-111446-5
	27.230 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	1-111446-4
	95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	1-111446-3
	89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	1-111446-2
	78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	1-111446-1
	70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	1-111446-0
	65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	111446-9
	57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	111446-8
	52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	111446-7
	47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	111446-6
	45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	111446-5
	39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	111446-4
	34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16	111446-3
	32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	111446-2
	27.230 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	111446-1
CONTACT FINISH	E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. H. MOLL 7-11-90 CHK. F.M. HEINEY 8-3-90		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLG ± 1 PLG ± 2 PLG ± 0.13[0.005] 3 PLG ± 4 PLG ± FINISH ANGLES ± CONTACTS: SEE TABLE		NAME: D. HOFFMAN PRODUCT SPEC: 108-1336 APPLICATION SPEC: 114-7011	
MATERIAL:  		SIZE: A1 CAGE CODE: 00779 DRAWING NO: 111446		RESTRICTED TO:	
CUSTOMER DRAWING		SCALE: 4:1		SHEET 1 OF 1 REV R	