

J O B B E R D R I L L S

Straight Shank

SM200 Worm Type Quick Helix

BS 328 DIN 338 ISO 235/1

Cobalt

Range

Finish


01 401 HSSE-8% Co1/8"-1/2"
3.00mm-13.00mmBright
Bright**01 405** HSSE-8% Co1/8"-1/2"
3.00mm-13.00mmTiN
TiN

Point Angle 135° Split Point

Designed for fast metal removal at high feeds and speeds.

Specially formulated flute (worm patt) and high helix angle for optimum swarf removal.

Cobalt 8% high speed steel for enhanced hot hardness.



Dia in d	Flute Length mm l ₂	Overall Length mm l ₁	01401 Availability	01405
1/8	3.00 33	61	•	•
	3.10 36	65	•	•
	3.20 36	65	•	•
	3.30 36	65	•	•
	3.40 39	70	•	•
	3.50 39	70	•	•
9/64	3.60 39	70	•	•
	3.70 39	70	•	•
	3.80 43	75	•	•
	3.90 43	75	•	•
5/32	4.00 43	75	•	•
	4.10 43	75	•	•
	4.20 43	75	•	•
	4.30 47	80	•	•
11/64	4.40 47	80	•	•
	4.50 47	80	•	•
	4.60 47	80	•	•
	4.70 47	80	•	•
3/16	4.80 52	86	•	•
	4.90 52	86	•	•
	5.00 52	86	•	•
	5.10 52	86	•	•
13/64	5.20 52	86	•	•
	5.30 52	86	•	•
	5.40 57	93	•	•
	5.50 57	93	•	•
7/32	5.60 57	93	•	•
	5.70 57	93	•	•
	5.80 57	93	•	•
15/64	5.90 57	93	•	•
	6.00 57	93	•	•
	6.10 63	101	•	•
	6.20 63	101	•	•
	6.30 63	101	•	•
1/4	6.40 63	101	•	•
	6.50 63	101	•	•
	6.60 63	101	•	•
	6.70 63	101	•	•
17/64	6.80 69	109	•	•
	6.90 69	109	•	•
	7.00 69	109	•	•
	7.10 69	109	•	•
	7.20 69	109	•	•
	7.30 69	109	•	•
	7.40 69	109	•	•
	7.50 69	109	•	•
	7.60 75	117	•	•
	7.70 75	117	•	•
	7.80 75	117	•	•
	7.90 75	117	•	•
	8.00 75	117	•	•
	8.10 75	117	•	•
	8.20 75	117	•	•
	8.30 75	117	•	•
	8.40 75	117	•	•
	8.50 75	117	•	•
	8.60 81	125	•	•
	8.70 81	125	•	•
	8.80 81	125	•	•
	8.90 81	125	•	•
	9.00 81	125	•	•
	9.10 81	125	•	•
	9.20 81	125	•	•
	9.30 81	125	•	•
	9.40 81	125	•	•
	9.50 81	125	•	•
	9.60 87	133	•	•
	9.70 87	133	•	•
	9.80 87	133	•	•
	9.90 87	133	•	•
	10.00 87	133	•	•
	10.10 87	133	•	•
	10.20 87	133	•	•
	10.30 87	133	•	•
	10.40 87	133	•	•
	10.50 87	133	•	•
	10.60 87	133	•	•