




5/8-24UNEF-2A

RECOMMENDED
CABLE STRIPPING DIM'S

FORMING

- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
- 1. BRASS PER QQ-B-626
 - 2. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 - 3. PHOSPHOR BRONZE PER QQ-B-750
 - 4. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 - 5. TEFLON MIL-P-19468

- 1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
- 2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .100"

5. TEFLON MIL-P-19468						DIMENSIONS ARE IN MILLIMETERS				PART NO. N6121A1-NT3G-1-50		Amphenol		
5 FERRULE COPPER NOTE 2 1 FR-648/533X 127C 4 CONTACT PIN NOTE 3 NOTE 4 1 N7000-4-3/11 3 BARREL NOTE 1 NOTE 2 1 N5000-3-46/31 2 INSULATOR NOTE 5 NATURAL 1 N5000-4T-50-A 1 BODY NOTE 1 NOTE 2 1 N7000-1						UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4				APPROVED DATE 10-11-01'				TITLE N CRIMP JACK
						SCALE 2.5/1		ISSUE A		CHECKED DATE 10-11-01'				DRAWING NO. KJ-N6121A1-NT3G-58CU-50
										DRAWN DATE 10-11-01'				ITEM NO.
										FILE NO				
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	2.5/1	ISSUE	A	FILE NO				