



Features:

- ✓ Designed for RG 59 Cable
- ✓ Quick three step installation process: Strip, Comb and Push-on.
- ✓ No Crimp tool required

Materials:

Connector Body: Gold plated brass

Ferrule: Gold plated annealed copper

Insulator: Delrin

Ratings:

Impedance: 75 ohms

Frequency: 0 to 500 MHz

VSWR: 1.5 max

Insulation Resistance: 5000 Megohms min.

Contact Resistance: 3 Milliohms max.

Voltage: *500Vrms

Temperature: -40 to 65 C

Durability: 500 matings

Cable Retention: 40lbs. min.

**Hands free testing in controlled voltage environment; For CE compliance: not intended for hand held use at voltages above 33Vrms/70 Vdc*

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060
For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com