

Isobar 4

SP&N type A distribution boards*



MGAN6



MGAN66SL

Note: All devices are sold separately

125A Standard A boards *(incomers not included)*

Part N°.	N°. of outgoing ways	Dimensions (mm)		
		Height	Width	Depth
MGAN6	6	264	260	127
MGAN9	9	264	315	127
MGAN12	12	264	370	127
MGAN15	15	264	450	127
*MGAN23	23	494	370	127

* 2 row unit.

125A Split load A boards *(incomers not included)*

Part N°.	Unprotected	Protected	Dimensions (mm)		
	outgoing ways	outgoing ways	Height	Width	Depth
MGAN46SL	4	6	264	450	127
MGAN48SL	4	8	264	450	127
MGAN66SL	6	6	264	450	127

Specification:

- Designed, manufactured and tested to BS EN 60439-3
- Unique Isobar outgoing phase connection link
- Busbar rating 125A
- Voltage rating 230/240Vac
- Distributed neutral allowing 2 pole switching at any outgoing way using distributed neutral kit
- Ingress protection IP31 to BS EN 60529
- Cable capacity neutral and earth bar 25mm²
- DIN rail mounting with fully shrouded busbars
- Surface or flush mounting using flush mounting kit, see page 11
- 5 single pole blanking plates
- Colour RAL 9001 epoxy powder coated
- IP2X with covers removed

Incomers:

Switch disconnecter	see page 10
Residual current device	see page 10
Terminal block	see page 10

Outgoers:

MCBs	see page 21
RCBOs	see page 22
2 pole Vigi	see page 23
Auxiliaries	see page 26

Distribution board accessories	see page 11
--------------------------------	-------------

* for use only with C60H range