

Product Families

- > [Automation](#)
- > [Sensing](#)
- > [LED Lighting & Signaling](#)
- > [Machine Safety](#)
- > [Industrial Components](#)
 - > [Pushbuttons & Pilot Devices](#)
 - > [L6 Series](#)
 - > [HW Series](#)
 - > [XA Series](#)
 - > [XW Series](#)
 - > [TWTD Series](#)
 - > [A8 Series](#)
 - > [AP Series](#)
 - > [A6 Series](#)
 - > [LW Silhouette Series](#)
 - > [LW Series](#)
 - > [TW Series](#)
 - > [XN Series](#)
 - > [CS CAM Switch Series](#)
 - > [ARN Series](#)
 - > [FB Series](#)
 - > [E-Stop Stations](#)
 - > [Circuit Breakers](#)
 - > [Power Supplies](#)
 - > [Relays And Sockets](#)
 - > [Solid State Relays](#)
 - > [Timers](#)
 - > [IEC Contactors](#)
 - > [Terminal Blocks](#)

HW1F-31F11QD-R-12V 22mm Selector Switch Lighted



MSRP: ****

[Add to Cart](#)

Key Features

- Finger safe (IP20) screw terminals standard, other terminal styles available
- All E-Stops meet EN418 (IEC compliant, positive action)
- UL listed, CSA certified, TUV approved, and CE marked
- Super bright incandescent or LED illumination
- IP65 and NEMA type 1, 2, 3, 3R, 4, 4X, 5, 12, and 13
- 600V/10A contacts with a wide operating range from 5mA at 3V AC/DC to 10A at 120V AC



Specifications

Literature

Downloads

Operation Type	Spring Return from Right
Product Type	Selector Switch Illuminated
Mounting Hole Size	Φ22mm
Shape	Round
Color	Red
Normally Open Contacts	1
Normally Closed Contacts	1
Number of Positions	3
Illumination Voltage	12V AC 12V DC