

**Xcelite**  
**5.45" Hard Wire (Piano and Music) Cutter with Blue Cushion Grip**  
**Handles**



**Product Details**

|                 |                                          |
|-----------------|------------------------------------------|
| Catalog No.     | 134CG                                    |
| UPC Code        | 037103059994                             |
| Description     | Transverse End Cutter                    |
| Jaw Type        | Flush                                    |
| Jaw Length      | 9 / 16 in.                               |
| Head Width      | 23 / 32 in.                              |
| Head Thickness  | 21 / 64 in.                              |
| Tip Dimensions  | Not Measured                             |
| Packaging       | Industrial Box / Carton                  |
| Tech. Spec.     | <a href="#">134CG Specifications.pdf</a> |
| Low Res. Image  | <a href="#">134CG 100.jpg</a>            |
| High Res. Image | <a href="#">134CG 300.jpg</a>            |
| Stock Item      | Normal Stock Item                        |

**Package Details (Dimensions)**

**Product Features:**

- Shear cutting action
- Ensures square cut ends
- Captures material on both sides of jaw, eliminates flying segments
- Patented spring loaded hold-down keeps material at 90° to tool blade
- Prevents material from forcing jaws apart
- Wire capacity .062"
- Stranded cable capacity 1 / 16"

**Xcelite**  
**5.45" Hard Wire (Piano and Music) Cutter with Blue Cushion Grip**  
**Handles**



| Individual Product |              |
|--------------------|--------------|
| Catalog No.        | 134CG        |
| UPC Code           | 037103059994 |
| Quantity           | 1            |
| Length (Inches)    | 5.8          |
| Width (Inches)     | 2.2          |
| Height (Inches)    | 0.8          |
| Gross Weight (lb)  | 0.2          |
| Volume (cu in)     | 10.208       |

| Catalog No.       | 134CG          |
|-------------------|----------------|
| I 2 of 5 Code     | 10037103059991 |
| Quantity          | 6              |
| Length (Inches)   | 6              |
| Width (Inches)    | 5.25           |
| Height (Inches)   | 2.375          |
| Gross Weight (lb) | 1.2            |
| Volume (cu in)    | 74.813         |

| Catalog No.       | 134CG          |
|-------------------|----------------|
| I 2 of 5 Code     | 20037103059998 |
| Quantity          | 48             |
| Length (Inches)   | 11.875         |
| Width (Inches)    | 10.875         |
| Height (Inches)   | 5.125          |
| Gross Weight (lb) | 9.6            |
| Volume (cu in)    | 661.846        |

# Pliers and Cutters - With Red Cushion Grip Handles




- The exceptional strength and performance of Xcelite® pliers and cutters are the result of forged alloy steel construction, precision machining, and scientific proportioning
- Handles designed to fit the hand comfortably and to provide maximum leverage
- Cleanly machined and perfectly aligned jaws grip tightly and surely while easy cutting is assured by hand-honed, mated cutting edges
- For extra working comfort all models have permanent, red plastic-coated “Cushion-Grip” handles except Combination Slip Joint pliers
- These high quality pliers and cutters are featured in Xcelite® Attachê Tool Cases



NOTE: When using cutting pliers always wear safety glasses to protect eyes from wire clippings

## Hard Wire (Piano and Music) Cutter 134CG



- Shear cutting action
- Ensures square cut ends
- Captures material on both sides of jaw, eliminates flying segments
- Patented spring loaded hold-down keeps material at 90° to tool blade
- Prevents material from forcing jaws apart
- Wire capacity .062
- Stranded cable capacity 1/16"

| Cat No. | UPC No.      | Packed | Length |     | A    |    | B    |      | C    |     | Pack Wt. |     | Shelf Pack |
|---------|--------------|--------|--------|-----|------|----|------|------|------|-----|----------|-----|------------|
|         |              |        | Inch   | mm  | Inch | mm | Inch | mm   | Inch | mm  | lb       | g   |            |
| 134CG   | 037103059994 | Boxed  | 5.45   | 140 | 0.55 | 14 | 0.72 | 18.5 | 0.32 | 8.2 | 18.4     | 522 | 6          |