



PRODUCT INFORMATION

tesa® 4341

Temperature resistant masking tape for paintwork. Its solvent free produced natural rubber adhesive offers well balanced properties in terms of tack, adhesion, shear- and temperature resistance.



close

<< || >>

**Product Features**

tesa 4341 is a finely creped, extremely stretchable and flexible paper masking tape for paintwork. Its solvent free produced natural rubber adhesive offers well balanced properties in terms of tack, adhesion, shear- and temperature resistance.

Technical Data

Backing material	slightly-creped paper
Total thickness	190 µm
Type of adhesive	natural rubber
Adhesion to steel	4.7 N/cm
Elongation at break	13 %
Tensile strength	53 N/cm
Temperature resistance	140 °C

Properties

Hand tearability	++
Easy to remove	yes
Paint anchorage	++
Sharp colour edge	+
Conformability	+

Evaluation across relevant tesa assortment: ++ very good, + good, o medium, - low

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to advise you.

tesa SE

Quickbornstraße 24
20253 Hamburg
Germany
Phone: +49 (40) 4909-101
Fax: +49 (40) 4909-6060
<http://www.tesa.de>