



Non-Ratcheting Crimper for Insulated/Non-Insulated Terminals and Soft Wire



The CK Tools 430024 is a multi-function non-ratchet action, specially hardened steel crimper with soft comfort grips.

CK Tools 430024 Features:

- Wire cutting: Soft wire only
- Crimping: Insulated terminals 1.5, 2.5, 6.0mm
- Crimping: Non-insulated terminals 1.5, 2.5, 4-6mm
- Bolt shearing: 2.6, 3.0, 3.5, 4.0, 5.0mm
- Wire stripping: 0.75, 1.0, 1.5, 2.5, 4.0, 6.0mm
- Length: 10"

Specification Name	Value
Replaceable / Interchangeable Dies	
Ratcheting	
Cutter Feature	
Stripper Feature	
Compatible with 4AWG	
Compatible with 6AWG	
Compatible with 8AWG	
Compatible with RG-6	
Compatible with RG-6S	
Compatible with RG-59	
Compatible with RG-62	
Compatible with RG-174	
Compatible with RJ-11	
Compatible with RJ-12	

Compatible with RJ-22	
Compatible with RJ-45	
Compatible with D-Sub Closed-Barrel	
Power Source	

Other Information	Value
Estimated Weight(lbs)	.564