



Wiha Adjustable TorqueControl Tools

Wiha TorqueControl Screwdrivers

- **TorqueFix** factory preset torque
- **TorqueVario** adjustable torque drivers

molded cushion grip two component handles allow for maximum achievable torque to be reached with comfort.

Precise repeatability!

All TorqueFix & TorqueVario tools are tested and comply with:

- **EN ISO 6798**
- **BS EN 26789**
- **ASME B107.14M**

Each tool has unique serial number and certificate of calibration

Whether it's TorqueVario-S or TorqueFix -
Wiha has a torque screwdriver to cover almost every application



+/-6% accuracy
tolerance Certificate
of calibration



+/-6% accuracy
tolerance Certificate
of calibration



285 TorqueFix, With Wiha-SoftFinish® Handle

Fixed Torque value pre-set. Tested in accordance with EN ISO 6798, BS EN 26789, ASME B107.14M, tolerance +/- 6%. Audible and perceptible click when pre-set torque has been attained. Automatically resets for next torque cycle; 50% greater reverse torque.

Item No.	Pre-Sets						
	oz.	lbs.	Nm	mm	Inch	lbs.	pkg.
285 03	80	5	0.56	112	4.4	.16	1
285 05	120	7.5	0.84	112	4.4	.15	1
285 07	160	10	1.12	119	4.7	.28	1
285 09	200	12.5	1.41	119	4.7	.27	1
285 11	240	15	1.69	119	4.7	.27	1
285 13	320	20	2.25	119	4.7	.28	1
285 15	400	25	2.82	126	4.9	.37	1
285 17	480	30	3.39	126	4.9	.37	1
285 18	560	35	3.95	126	4.9	.37	1
285 19	640	40	4.52	126	4.9	.37	1
285 21	800	50	5.65	132	5.2	.52	1
285 23	960	60	6.78	132	5.2	.52	1
285 25	1120	70	7.91	132	5.2	.52	1

285 Adjustable TorqueVario With Direct Reading Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Range					
	Inch	lbs.	Increments	mm	lbs.	pkg.
285 01*	15 - 80(in/oz)		2.5 Inch oz	122 - 127	.22	1
285 02	5 - 10		.2 Inch lbs	122 - 127	.41	1
285 04	7.5 - 20		.5 Inch lbs	126 - 131	.50	1
285 06	10 - 50		2 Inch lbs	133 - 138	.59	1
285 08	20 - 70		2 Inch lbs	137 - 142	.74	1

Above includes Micro Bit Holder 28583

[See 4mm Micro Bits on Page 159-160](#)

* +/- 10% (This unit only)



+/-6% accuracy tolerance
Certificate of calibration



285 Adjustable TorqueVario-S Handle - In Newton Meter Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Newton Meter Scale					
		Increments	mm	lbs.	pkg.	
285 50*	0.1 - 0.6Nm	.02 Nm	122 - 127	.35	1	
285 51	0.4 - 1.0Nm	.05 Nm	122 - 127	.35	1	
285 52	0.8 - 2.0Nm	.05 Nm	126 - 131	.45	1	
285 53	1.0 - 5.0Nm	.20 Nm	133 - 138	.55	1	
285 54	2.0 - 8.0Nm	.25 Nm	137 - 142	.70	1	

* +/- 10% (This unit only)

All TorqueVario models
include Torque setting
adjustment tool