



## Overview

Presentation	Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments.
Lead time	Usually in Stock

## General

Provided equipment	Casters Key(s) Leveling feet Rack power distribution unit (PDU) Side panels Unpacking sheet
--------------------	--

## Physical

Maximum mounting depth	88.01 cm
Number of rack unit	38U
Minimum mounting depth	72.01 cm
Colour	Grey Oak
Depth	113 cm
Rack width	19"
Height	195 cm
Net weight	202.5 kg
Permanent permissible load	778.36 kg static
Width	75 cm

## Input

Network frequency	50/60 Hz
Plug standard	IEC 60320 C14

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input voltage	200 V 208 V 230 V 240 V
---------------	----------------------------------

## Conformance

Product certifications	TAA compliance
Standards	EIA-310D

## Packing Units

Package 1 Weight	230 kg
Package 1 Height	215 cm
Package 1 width	80 cm
Package 1 Length	120 cm
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------