




- 1 TIN PL .000150 MIN THK PER ASTM B 545
- 2 PART NO: 324466; .243 LB. PART NO: 1-324466-0; .243 LB. PART NO: 2-324466-1; .243 LB. PART NO: 2-324466-2; .269 LB.
- 3 RED COLOR CODE
- 4 CLEANED, UNPLATED
- 5 .045 MAX BURR ALLOWED INSIDE THE WIRE BARREL ID IN AREA OF SIGHT HOLE.

OBSOLETE	1.07	1.32	2.64	△	450-550 MCM	COPPER ASTM-B-75 ANNEALED	2-324466-2
	1.07	1.07	2.41	△			2-324466-1
				△			1-324466-0
				△			324466
	"C"	"B"	"A"	FINISH	WIRE RANGE	MATERIAL	PART No
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN DK SCHRUM 4/24/89	TE Connectivity		
DIMENSIONS: INCHES				CHK MS FEHER 4/24/89			
				APVD WJ VOCKROTH 11/8/89	NAME SPLICE, BUTT, AMPPOWER WIRE SIZE: 500 MCM		
				PRODUCT SPEC			
MATERIAL SEE TABLE				APPLICATION SPEC	SIZE A3 CAGE CODE 00779 DRAWING NO C=324466		
				FINISH SEE TABLE			
				WEIGHT △	RESTRICTED TO		
				CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1	REV R