


CONFIDENTIAL

VERTRAULICH

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Veruegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.


THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

1	2	3	4
recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
	0.75 to 1	30 +0.1	22.2 +0.2
	>1 to 1.5	30.2 +0.1	22.2 +0.2
	>1.5 to 3	30.4 +0.1	22.2 +0.2




Marking
MARQUARDT®
1661.
16(4)/250~ T85/55

12 A 125-250 V AC
1/6 HP 125V AC
1/2 HP 250 V AC
R 84



Code of manufacture: place/year/week

DPST
Total travel 4±0.4
Suitable for appliances of class II



-	-	-	1661.0220-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location Angle ± 2 ° Edge tolerance ⊙ ≡	Length		Sheet 01
	Radii		Ident. K
	All dimensions are in millimetres		Document number 16610220
	Appliance Switch		Index f
f	137245	2021-04-30	JOSHIO
e	32547	2002-05-23	SIG
d	28075	1999-10-12	MUT
c	26325	1998-09-30	BB
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
MARQUARDT		System NX V1872	Replacement of
		Zg.gl.Nr.v.30.09.1998	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Marquardt:

<u>1661.0220</u>	<u>1667.0102</u>	<u>1660.5853</u>	<u>1661.0120</u>	<u>1662.0301</u>	<u>1663.0201</u>	<u>1660.5205</u>	<u>1665.5504</u>	<u>1660.0223</u>	<u>1660.0203</u>
<u>1660.5201</u>	<u>1665.3101</u>	<u>1660.0407</u>	<u>1662.0102</u>	<u>1660.5202</u>	<u>1660.8204</u>	<u>1661.5201</u>	<u>1662.0103</u>	<u>1662.0106</u>	<u>1667.0104</u>