

GP Batteries

Data Sheet


Model No.: GP14A

NO MERCURY ADDED

Description	: Mercury Free Alkaline Manganese Battery, C Size
Chemical System	: Alkaline Manganese
Nominal Voltage	: 1.5 Volts
Nominal Dimensions	: Ø26.2 mm x 50.0 mm
Terminals	: Protruded positive(+) and flat negative(-) contacts
Jacket	: Foil jacket
Applications	: All electronic devices, e.g. transistor radios, cassette recorders, toys, alarm clocks, lighting & torches, portable fans.
Shelf Life	: 36 months
Average Weight	: 70g
Date Code	: Unless otherwise specified, every battery will carry an expiry date code for 36 months. (e.g. a battery manufactured in January 1999 will carry an expiry date code of 01-02.) 01 stands for January, 02 stands for 2002

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
3.9 Ohms	24 Hrs/ Day	0.75V	19 Hrs
39 Ohms	4 Hrs/ Day	0.9V	235Hrs



Cross References:

GP	JIS	IEC	Eveready	Duracell	Varta
14A	LR14	LR14	E93	MN1400	4014

