



DATA SHEET	0068000
ÖLFLEX® HEAT 180 SiD	valid from : 10.12.2007

Application

ÖLFLEX® HEAT 180 SiD are silicone-single cores and recommended for use in the case of high ambient temperatures under sufficient ventilation and low mechanical stress. In the case of room temperature, ÖLFLEX® HEAT 180 SiD is largely resistant against oil, alcohol, acids, caustic solutions, salt solutions and salt water.

Design

Conductor	solid conductor made of tinned copper
Core insulation	Silicone based compound EI2 acc. to HD 22.1 resp. VDE 0282-1
Core identification	coloured

Electrical properties at 20 °C

Nominal voltage	300 / 500 V
Test voltage	2000 V AC

Mechanical and thermal properties

Temperature range	-50 °C up to +180 °C max. conductor temperature pay attention to sufficient ventilation, if ignoring the max. conductor temperature is +100 °C.
Min. bending radius	10 x cable diameter for fixed installation
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2 after combustion a SiO ₂ -ash skeleton remains, which has still good insulation properties but has no more any mechanical stability.
Halogen-free	acc. to IEC 60754-1 resp. VDE 0472 part 815
Corrosivity	acc. to IEC 60754-2 resp. VDE 0482 part 267-2-3
Tests	in acc. to IEC 60811-x-x resp. VDE 0473 part 811-x-x, VDE 0472
EC directive	this cable confirms to ECD 2006/95/EC (low voltage directive).

elaborated by: TE-K: M. Herb / R. Krämer	Document: DB0068000EN	page 1 of 1
---	-----------------------	-------------