

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 19058-0026
Status: Active
Description: RING AVIKRIMP H/D (B-801-76HD)

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series 19058
Crimp Quality Equipment Yes
Mil-Spec N/A
Product Name Avikrimp™
Type Ring
UPC 800753059214

Physical

Barrel Type Closed
Flammability 94V-2
Insulation Nylon (PA)
Material - Plating Mating Tin
Net Weight 4.362/g
Packaging Type Bag
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Stud Size 7/16" (M11)
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 5.70mm max.
Wire Size AWG 14, 16
Wire Size mm² 1.30 - 2.00

Material Info

Old Part Number B-801-76HD

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing BHD80101




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19058Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade™	0640010100
Hand Crimp Tool	
Crimp Head for the	0640050100
AT-200™ Pneumatic	
Hand Tool	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19058-0026](#)