



531 224
 236
 plus
 388
 479


Type	Side Walls	Pg Knockouts	Inside Height	Ref. No.	Unit																											
POLYSTYRENE - COVER GREY RAL 7035																																
PS 99- 6	with Pg		45 mm	115-403	40/4																											
PS 99- 8	with Pg		69 mm	115-903	30/3																											
PS 99- 6-o	smooth		45 mm	110-403	40/4																											
PS 99- 8-o	smooth		69 mm	110-903	30/3																											
POLYSTYRENE - COVER TRANSPARENT																																
PS 99- 6-t	with Pg		45 mm	116-003	40/4																											
PS 99- 8-t	with Pg		69 mm	116-503	30/3																											
PS 99- 6-to	smooth		45 mm	111-003	40/4																											
PS 99- 8-to	smooth		69 mm	111-503	30/3																											
POLYCARBONATE - COVER GREY RAL 7035																																
PC 99- 6	with Pg		45 mm	125-403	40/4																											
PC 99- 8	with Pg		69 mm	125-903	30/3																											
POLYCARBONATE - COVER TRANSPARENT																																
PC 99- 6-t	with Pg		45 mm	135-003	40/4																											
PC 99- 8-t	with Pg		69 mm	135-503	30/3																											
Knockouts: = Pg 16/11 = Pg 16 = Pg 21/16 = Pg 29/21																																
					Max. number of Pg drill holes per box side <table><thead><tr><th>Pg</th><th>A</th><th>B</th></tr></thead><tbody><tr><td>7</td><td>3</td><td>3</td></tr><tr><td>9</td><td>2</td><td>2</td></tr><tr><td>11</td><td>2</td><td>2</td></tr><tr><td>13.5</td><td>2</td><td>2</td></tr><tr><td>16</td><td>2</td><td>2</td></tr><tr><td>21</td><td>-</td><td>-</td></tr><tr><td>29</td><td>-</td><td>-</td></tr><tr><td>36</td><td>-</td><td>-</td></tr></tbody></table>	Pg	A	B	7	3	3	9	2	2	11	2	2	13.5	2	2	16	2	2	21	-	-	29	-	-	36	-	-
Pg	A	B																														
7	3	3																														
9	2	2																														
11	2	2																														
13.5	2	2																														
16	2	2																														
21	-	-																														
29	-	-																														
36	-	-																														
All dimensions in millimeters																																

TK 99
Empty
Enclosure
94 x 94^{mm}
Type of
Protection
IP 66

TK 99
A winner -
universal thanks
to the generous
range of
accessories
and various
cover heights.



<i>Description</i>	<i>Ref. No.</i>	<i>Page</i>
Mounting plate	195-003	61
Mounting rail TS 15/75	Z-630	61
Hinge kit	190-002	61
Wall plate kit	194-001	61



A complete
overview
of the system
accessories
is given
on pages
58 - 63.