



NOTES:

1. ALL DIMENSION IN MM [INCH]
 2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
 3. TERM. NOS. FOR REF. ONLY
 4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
 5. CONTACT RATING (NON-SWITCHING) 5A
 6. CONTACT MATERIAL: SILVER OVER COPPER ALLOY
 7. OPERATING FORCE: 425 ± 100 CM/STANDARD
 8. OPERATING TEMP: -30° to 85° C
 9. CIRCUIT DP: 4 POSITIONS, 30° INDEX.
 10. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL
 11. ▲ DESIGNATE MAJOR DIMENSIONS
 12. HARDWARE SUPPLIED ON SWITCH – SEE BELOW
- STOPRING, LOCKWASHER, & HEXNUT





CONTACT CONFIGURATION

Timing: Shorting



TERMINATION DETAIL

SCALE 2X



E-SWITCH®			
C	12821	REVISED NOTE 12	CJB
B	12579	REV DESC PER NEW CATALOG	CJB
A	11499	RELEASED FOR PRODUCTION	CJB
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE		DATE	DR
1.5:1		5/15/01	CJB
TITLE		DATE	DWG
KC-24A (9.5mm) 01-S-L-S		5/15/01	G510897
REV		DATE	REV
			C