

Part Number: **5973305602F**

General Description	
Series	597
Configuration	'0805(2.0MM X 1.25MM X 0.7MM)
Description	SMD LED 0805 G Sample Strip
Package Options	Sample Strip
Lamp Type	Single Color
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Â°)	
Forward Current mA	30mA
Reverse Current	100 @ Vr =5V
Forward Current Pulsed	100mA
Derating	from 50Â° @ .6mA/Â°C
Solder Temperature	260Â° for 5 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics	
Color	Green
Luminous Intensity Min	4
Luminous Intensity Typical	8
Test Current mA	-
Power Dissipation Max	114mW



5973305602F

check stock



[This is a
RoHS Compliant Product.
To learn more click here](#)