



D


C

B

A



1. 相手ハウジングと所定の機能を満たして嵌合できること。
2. フードの反りは0.2以内。
3. 推奨取付ねじ：JIS B 1115 又は、1122 タッピンねじ
なべ1種、呼び径3を使用し、締め付け後半田付けする。
(締め付けトルク：0.4N・m 以下)
4. 適用製品規格：108-5093
5. [A] 面より2mmの範囲で測定。
6. 相手ハウジングとの嵌合力は、29.4N以下。
但し、リセプタクル コンタクトは含まない。
1. IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION.
2. WARPAGE 0.2 MAX.
3. RECOMMENDED MOUNTING SCREW: 3mm DIA,
PAN HEAD, CLASS 1 TAPPING SCREW SPECIFIED IN JIS
B1115, B1122 (TORQUE: 0.4N・m MAX.)
4. PRODUCT SPECIFICATION: 108-5093
5. TO BE MEASURED WITHIN 2mm FROM [A]
6. IN COUPLING WITH THE PLUG HOUSING MATING FORCE
29.4N MAX. WITHOUT RECEPTACLE CONTACTS.



	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD	NATURAL	1-5172034-1
	SEE CUSTOMER DRAWING 8-172034-1			8-172034-1
	PRE-TIN		NATURAL	5-172034-4
	PRE-TIN		NATURAL	4-172034-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD	GREEN	2-172034-4
OBSOLETE	TIN-LEAD	SELECTIVE GOLD	NATURAL	2-172034-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD	GREEN	1-172034-4
OBSOLETE	TIN-LEAD	SELECTIVE GOLD	NATURAL	1-172034-1
	PRE-TIN		YELLOW	172034-7
	PRE-TIN		GRAY	172034-6
	PRE-TIN		BLUE	172034-5
OBSOLETE	PRE-TIN		GREEN	172034-4
	PRE-TIN		BROWN	172034-3
	PRE-TIN		BLACK	172034-2
	PRE-TIN		NATURAL	172034-1
	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
	CONTACT FINISH コンタクト仕上			

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差
0<×≤ 10 : ±0.2
10<×≤ 30 : ±0.25
30<×≤ 100 : ±0.3
ANGLE : ±3°
角度

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.YUASA 7/21'92	TE Connectivity		
DIMENSIONS: mm		CHK K.YUASA 7/21'92			
		APVD A.TOMITA 7/21'92	NAME MULTI-INTERLOCK CONNECTOR 11P VERTICAL TYPE CAP HOUSING ASSEMBLY		
		PRODUCT SPEC SEE NOTE 4			
MATERIAL HOUSING: 66NYLON TAB CONTACT: BRASS		FINISH SEE TABLE	SIZE A2	CAGE CODE 00779	DRAWING NO C=172034
			WEIGHT 0	RESTRICTED TO —	
			CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
				REV F4	