

Trust Thomas and Betts for all your wiring accessories!

Features include:

- Divider Walls, enabling multiple channels to be created within a duct channel
- Universal Mounting Clips that secure channels and wires
- Corner Strips that keep corners rigid at tee junctions when used for control panel applications
- Joining Strips to unite sections of duct and keep the wall rigid
- Plastic Rivets for securing ducts quickly and easily

[_] = space for colour identifier:

G = Grey


W = White

B = Black

I = Intrinsic Blue

Create multiple channels
inside wiring ducts!

Divider Wall



- Separates high and low voltage to reduce shortages and interference
- Mount inside any Ty-Duct™ PVC wiring duct using Universal Mounting Clips
- Score lines enable sections to be removed
- Solid and Wide Slotted style

CAT. NO.	DESCRIPTION	LENGTH (FT.)	STD. CTN. QTY
TY1D[_]P[_]6	1" High Wall Divider	6	120
TY1.5D[_]P[_]6	1.5" High Wall Divider	6	120
TY2D[_]P[_]6	2" High Wall Divider	6	120
TY3D[_]P[_]6	3" High Wall Divider	6	120
TY4D[_]P[_]6	4" High Wall Divider	6	120
TY5D[_]P[_]6	5" High Wall Divider	6	120

Catalogue Number must be completed by adding suffix S for Solid or W for Wide Slot.


Example: TY2DSPG6 is a 2" high solid wall grey divider.

Catalogue Number must be completed by adding suffix G for Grey, W for White, I for Intrinsic Blue, B for Black.

Example: TY2DSPG6 is a 2" high solid wall grey divider.

One size fits all!

Universal
Mounting
Clips




- Added before or after the duct is in place, without additional hardware
- Twists on into place —holds securely
- Installs easily using a screwdriver
- Accommodates up to 40 lb. cable ties
- Black polycarbonate

CAT. NO.	DESCRIPTION	QTY
UMC	Universal Fastener Mount	100 pk

Install smooth round corners on your wiring duct!

Corner Strips



- Constructed of rigid PVC
- One-piece design makes installation a snap
- Works with any Ty-Duct™ wiring duct
- Select from a variety of sizes


CAT. NO.	DESCRIPTION	LENGTH (FT.)	STD. CTN. QTY
TYCS[_]6	Corner Strip	6	120

Catalogue Number must be completed by adding suffix G for Grey, W for White, I for Intrinsic Blue, B for Black.

Example: TYCSG6 is a grey corner strip.

Plastic rivets make mounting ducts easy!

Plastic Rivets




- Fast installation
- Durable and economical
- One size

CAT. NO.	DESCRIPTION	QTY
08200C	3/16" Plastic Rivet	100 pk
08200M	3/16" Plastic Rivet	1000 pk

Join duct sections easily!

Joining Strips




- Slides on duct
- Constructed of rigid PVC
- One-piece design makes installation easy
- Works with any Ty-Duct wiring duct


CAT. NO.	DESCRIPTION	LENGTH (FT.)	STD. CTN. QTY
TYJS[_]6	Joining Strip	6	120

Catalogue Number must be completed by adding suffix G for Grey, W for White, I for Intrinsic Blue, B for Black.


Example: TYJSG6 is a grey joining strip.



Minimum mounting rivet distance for ducts less than 1½" wide.




Minimum mounting rivet distance for ducts 1½" to 2½" wide.



Minimum mounting rivet distance for ducts greater than 2½" wide. Installed top and bottom.

Wiring Duct and Accessories



Original Slot Duct (chlorine free) *Noryl®

Noryl Cat. No.		Nom. Size		Dimensions-Inches									
Duct	Cover	W	H	A	B	C	D	E	F	G	H	J	K
-	-	.50	.50	.62	.50	.75	.56	.62	.38	on ctr.	.50	-	-
-	-	.50	1.00	.62	1.00	.75	1.10	.73	.63	on ctr.	.50	.31	.20
-	-	.50	1.25	.62	1.25	.75	1.35	.73	.52	on ctr.	.50	.31	.20
-	-	.75	.75	.86	.75	1.06	.88	.62	.38	on ctr.	.50	-	-
-	-	.75	1.25	.86	1.25	1.06	1.35	.73	.52	on ctr.	.50	.31	.20
-	-	.75	1.50	.86	1.50	1.06	1.60	.73	1.00	on ctr.	.50	.31	.20
51000	-	1.00	1.00	1.13	1.00	1.38	1.10	.73	.52	on ctr.	.50	.31	.20
51120	-	1.00	1.25	1.13	1.25	1.38	1.35	.73	.52	on ctr.	.50	.31	.20
51150	-	1.00	1.50	1.13	1.50	1.38	1.60	.73	1.00	on ctr.	.50	.31	.20
51020	50010	1.00	2.00	1.18	2.00	1.38	2.10	.73	1.25	on ctr.	.50	.38	.38
51030	50010	1.00	3.00	1.18	3.00	1.38	3.10	1.00	2.25	on ctr.	.50	.38	.38
51040	50010	1.00	4.00	1.20	4.00	1.38	4.10	1.00	3.25	on ctr.	.50	.38	.38
51510	-	1.50	1.00	1.63	1.00	1.88	1.10	.73	.52	on ctr.	.50	.31	.20
-	-	1.50	1.50	1.63	1.50	1.88	1.60	.73	1.00	on ctr.	.50	.31	.20
51520	50015	1.50	2.00	1.68	2.00	1.88	2.10	.73	1.25	on ctr.	.50	.38	.38
51530	50015	1.50	3.00	1.68	3.00	1.88	3.10	1.00	2.25	on ctr.	.50	.38	.38
51540	50015	1.50	4.00	1.70	4.00	1.88	4.10	1.00	3.25	on ctr.	.50	.38	.38
52010	-	2.00	1.00	2.13	1.00	2.38	1.10	.73	.52	.50	.50	.31	.20
52150	-	2.00	1.50	2.13	1.50	2.38	1.60	.73	1.00	.50	.50	.31	.20
52020	-	2.00	2.00	2.18	2.00	2.38	2.10	.73	1.25	.50	.50	.38	.38
52030	50020	2.00	3.00	2.18	3.00	2.38	3.10	1.00	2.25	.50	.50	.38	.38
52040	50020	2.00	4.00	2.20	4.00	2.38	4.10	1.00	3.25	.50	.50	.38	.38
52050	50020	2.00	5.00	2.20	5.00	2.38	5.10	1.50	4.25	.50	.75	.50	.38
-	-	2.50	3.00	2.68	3.00	2.88	3.10	1.00	2.25	on ctr.	.50	.38	.38
-	-	3.00	1.00	3.13	1.00	3.38	1.10	.73	.52	1.00	.50	.31	.20
53120	-	3.00	1.25	3.13	1.25	3.38	1.35	.73	.52	1.00	.50	.31	.20
-	-	3.00	2.00	3.18	2.00	3.38	2.10	.73	1.25	1.00	.50	.38	.38
53030	50030	3.00	3.00	3.18	3.00	3.38	3.10	1.00	2.25	1.00	.50	.38	.38
53040	50030	3.00	4.00	3.20	4.00	3.38	4.10	1.00	3.25	1.00	.50	.38	.38
53050	50030	3.00	5.00	3.20	5.00	3.38	5.10	1.50	4.25	1.00	.75	.50	.38
-	-	4.00	1.00	4.20	1.00	4.38	1.10	.73	.52	1.50	.50	.31	.2
54020	-	4.00	2.00	4.20	2.00	4.38	2.10	.73	1.25	1.50	.50	.38	.38
54030	50040	4.00	3.00	4.18	3.00	4.38	3.10	1.00	2.25	1.50	.50	.38	.38
54040	50040	4.00	4.00	4.20	4.00	4.38	4.10	1.00	3.25	1.50	.50	.38	.38
54050	50040	4.00	5.00	4.20	5.00	4.38	5.10	1.50	4.25	1.50	.75	.50	.38

• Standard lengths are 6 feet


To order Adhesive-backed Duct, add suffix A to Catalogue Number. Example: 52020A is a 2" x 2" grey duct with adhesive backing. Shelf life for adhesive is 1 year.

Note: Noryl® duct is available in oyster white only. UL 94 V-1


*Noryl® is a registered trademark of Sabic Innovative Plastics IP B.V. Company

Temp. rating: 95°C


Low temp. (under IZOD impact test): -40°C



Typical Side View




Overall Height
Cover Installed



Bottom Mounting
Holes, 1/2 x 3/16

Wiring Duct and Accessories



Solid Wall Duct (chlorine free) *Noryl®


Noryl Cat. No.		Nom. Size		Dimensions-Inches				
Duct	Cover	W	H	A	B	C	D	E
-		.50	.50	.62	.50	.75	.56	on ctr.
-		.50	1.00	.62	1.00	.75	1.10	on ctr.
-		.50	1.25	.62	1.25	.75	1.35	on ctr.
-		.50	1.75	.62	1.75	.75	1.88	on ctr.
-		.50	2.00	.62	2.00	.75	2.10	on ctr.
-		.75	.75	.86	.75	1.06	.88	on ctr.
-		.75	1.00	.86	.75	1.06	1.10	on ctr.
-		.75	1.25	.86	1.25	1.06	1.35	on ctr.
-		.75	1.50	.86	1.50	1.06	1.60	on ctr.
-		.75	2.00	.86	2.00	1.06	2.10	on ctr.
U51000		1.00	1.00	1.13	1.00	1.38	1.10	on ctr.
U51125		1.00	1.25	1.13	1.25	1.38	1.35	on ctr.
U50115		1.00	1.50	1.13	1.50	1.38	1.60	on ctr.
U50102	50010	1.00	2.00	1.18	2.00	1.38	2.10	on ctr.
U50103		1.00	3.00	1.18	3.00	1.38	3.10	on ctr.
U50104		1.00	4.00	1.20	4.00	1.38	4.10	on ctr.
-		1.50	1.00	1.63	1.00	1.88	1.10	on ctr.
U50155		1.50	1.50	1.63	1.50	1.88	1.60	on ctr.
U50152	50015	1.50	2.00	1.68	2.00	1.88	2.10	on ctr.
U50153		1.50	3.00	1.68	3.00	1.88	3.10	on ctr.
U50154		1.50	4.00	1.70	4.00	1.88	4.10	on ctr.
U50201		2.00	1.00	2.13	1.00	2.38	1.10	.50
U50215		2.00	1.50	2.13	1.50	2.38	1.60	.50
U50202		2.00	2.00	2.18	2.00	2.38	2.10	.50
U50203	50020	2.00	3.00	2.18	3.00	2.38	3.10	.50
U50204		2.00	4.00	2.20	4.00	2.38	4.10	.50
U50205		2.00	5.00	2.20	5.00	2.38	5.10	.50
-		2.50	3.00	2.68	3.00	2.88	3.10	on ctr.
-		3.00	1.00	3.13	1.00	3.38	1.10	1.00
U53125		3.00	1.25	3.13	1.25	3.38	1.35	on ctr.
-		3.00	2.00	3.18	2.00	3.38	2.10	1.00
U50302	50030	3.00	3.00	3.18	3.00	3.38	3.10	1.00
U50304		3.00	4.00	3.20	4.00	3.38	4.10	1.00
U50305		3.00	5.00	3.20	5.00	3.38	5.10	1.00
-		4.00	1.00	4.20	1.00	4.38	1.10	1.50
U50402		4.00	2.00	4.18	2.00	4.38	2.10	1.50
U50403	50040	4.00	3.00	4.18	3.00	4.38	3.10	1.50
U50404		4.00	4.00	4.20	4.00	4.38	4.10	1.50
U50405		4.00	5.00	4.20	5.00	4.38	5.10	1.50

• Standard lengths are 6 feet.


Adhesive backed duct in solid wall style is a custom order. Consult customer service for availability.

Note: Noryl® duct is available in oyster white only. UL 94 V-1


*Noryl® is a registered trademark of Sabic Innovative Plastics IP B.V. Company



Typical Side View



Overall Height
Cover Installed



Bottom Mounting
Holes, 1/2 x 3/16

Vinyl duct is UL Recognized , UL 94 V-0 rated
CSA Certified and meets the JIC requirements.