









L Type



S Type



FEATURES:

Half pitch 1.27mm(.050") series
Centronic female connector solder
type for cable

Panel mount receptacle assemblies
bracket with latch block and
without latch block

Die-cast body provide EMI/RFI shielded

MATERIALS:

Housing:

Thermoplastic P.B.T UL94V-0 black

Contacts:

Phosphor bronze mating end selective
gold plated

Shell: Steel nickel plated over copper

Shell: Steel nickel plated over copper

ELECTRICAL:

Current Rating: 1 Amp

Insulation Resistance: 500M Ω /in

Withstanding Voltage: AC 500V/Min

Contact Resistance: 35m Ω MAX

Temperature Range: -55°C ~ +105°C



SERIES

Solder termination

NUMBER OF CONTACT:

CONTACT TYPES:

F = female

CONTACT PLATING:

0 = selective flash gold

1 = selective 15u" gold

2 = selective 30u" gold

FIXING DEVICE :

L : Latching + Jackscrews

S : Jackscrews only

THREADED HOLES:

1 : UNC # 2-56

2 : UNC #4-40

3 = M2.6

Amphenol Socapex

Usine de Dole

ECH. ENS.

N SERIE

DATE DU TIRAGE

DESIGNATION

DOSSIER

MINI D SERIES

TOL. GEN.

VOLUME PIECE

SURFACE PIECE

PROTECTION

TRAITEMENT

MATIERE

CLIENT

MODIFICATIONS

EXEC. DATE

ATO 30/05 2005

ATO

IND.

N INTERNE

MD5 SC 50F

COMMUNICATION ET UTILISATION INTERDITES SAUF AUTORISATION