

NOTICE: All drawings and specifications are and remain our property and must be returned to us. All specifications are confidential and are not to be disclosed to any persons other than those to whom they are sent. No drawings, specifications or other data belonging to us which may be furnished to vendors for production or quotation are to be regarded by implication or otherwise as in any manner licensing the holder or any other person or corporation or conveying any rights or permission to manufacture, use or sell any patented design or product that may in any way be related thereto.

REMOVE ALL BURRS, BREAK CORNERS AND SHARP EDGES .005 MAXIMUM UNLESS OTHERWISE SPECIFIED.


DO NOT SCALE THIS DRAWING

16750
DRAWING NUMBER


ISSUE
1

REVISIONS

ZONE	SYM.	DESCRIPTION	DATE	ECONO	APPR.
	D	REDRAWN- NO CHANGE	8-14-62	5934	G
	E	OFF. ENG. REL. TO PROD.	5-14-63	8587	W
	F	ITEMS 4+5 1 PC. TO FIMPH.	3-17-63	9210	RFD
2B	G	ITEM 6 WAS 2408	1-3-64	9764	RTW
	H	ITEM 7 WAS 2800 & ITEM 8 WAS 2800 & ITEM 9 WAS 2800 & ITEM 10 WAS 2800	2-11-64	9051	AER
	J	ADDED NOTE, UPDATED OVER BALLBOONS. ITEM 6 WAS 82-950, ITEM 5 WAS 2-13A-05	7/29/65	12198	S.P.
	K	ADDED.	1-19-66	12893	AR
	L	ITEM 4 WAS 82-947	4-19-66	13274	AR
	M	REVISED PLATING NOTES	11/7/75	22593	E.V.H.
	N	ADDED CABLE STRIPPING DIM	6/30/78	26119	RM
	P	CHANGED WORD "ROLL" TO "STAKE"	8/1/83	29464	SES DR



SECTION AA



RECOMMENDED STRIPPING DIM

NOTES:

1. CHROMIUM TREAT PER FS-100-11.
2. Astroplate .00005/.0001 thick per Para. 3.2.1.1 of Amphenol Spec. 349-50060
3. Astroplate .00017/.00015 thick per Para. 3.2.1.2 of Amphenol Spec. 349-50060

REQ	ITEM	PART NO.	DESCRIPTION	FINISH
1	10	29106	CLAMP GASKET	
1	9	29105	CLAMP WASHER	SEE NOTE 3
1	8	29102	CLAMP NUT	SEE NOTE 3
1	7	29103	BRAID CLAMP	SEE NOTE 3
1	6	82-1535-21	GASKET	
1	5	82-1138-2	SPRING RING	
1	4	82-2304-1	COUPLING NUT	SEE NOTE 3
1	3	16753	MALE CONTACT	FS-100-6
1	2	16752	INSULATOR (TEFLON)	
1	1	16751	BODY	SEE NOTE 2

LIST OF MATERIAL AMPHENOL RF

A DIVISION OF
AMPHENOL-BORG ELECTRONICS CORP.
GENERAL OFFICES
DANBURY, CONN.
PLANTS AT
CHICAGO 38, ILL. WOODSIDE 77, N.Y.
DANBURY, CONN.

OFFICIAL ENG. REL.
8587
5-17-63

NEXT ASSY. USED ON
APPLICATION

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCE ON
FRACTIONS DECIMALS ANGLES
± 1/64 ± .005 ± 1/2°
MATERIAL 11
SPECIFICATION 11
FINISH
SEE LIST OF MATERIAL

DRAWN BY
GIDAL
CHECKED
8-14-62
ENGINEER
DATE
APPROVED
DATE
REFERENCE DRAWING NO

TITLE
HN PLUG
FOR RG-55458/U CABLE

CODE IDENTIFICATION
DRAWING SIZE
DRAWING NO
16750
ISSUE
P
SCALE 2-1
SHEET OF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[16750](#)