

Pre-Printed Pre-Cut Blank Sign Headers (B-595)

For creating Arc Flash and safety warning labels in seconds.


- Allows printer to create multicolor signs fast - in a single print pass
- Headers meet NFPA 70E, OSHA 1910.145 and ASME/ANSI Z535 standards
- Indoor/outdoor grade material conforms to rough, highly textured, and "difficult to adhere to" surfaces

Service temp: -40°F to 180°F Application temp: 0°F to 180°F
Average Outdoor Durability: 8-10 years

Use these supplies with templates in the BBP®33 printer & MarkWare™ Software for arc flash labels and safety warning labels



Figure 70



Fits Printer Model(s)	Diagram	Catalog #	Header	Label Height A Inch (mm)	Label Width B Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 70	B30-241-595-OSHADA		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-25-595-OSHADA		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-241-595-OSHACA		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-25-595-OSHACA		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-241-595-ANSICA		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-25-595-ANSICA		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-241-595-ANSIDA		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-25-595-ANSIDA		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-241-595-ANSIWA		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-25-595-ANSIWA		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-241-595-ANSINO		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-25-595-ANSINO		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-242-595-BLNKWT		1.125 (28.6)	2.850 (72.4)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-241-595-BLNKWT		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-219-595-BLNKWT		2.250 (57.5)	3.850 (97.8)	1	250	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-25-595-BLNKWT		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-241-595-BLNKYL		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000 (black or colors)
BBP31, BBP33	Fig. 70	B30-25-595-BLNKYL		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000 (black or colors)

*Pre-sized to fit blank rigid valve tags but can also be used on its own as general purpose label. **Text area below header is yellow. Text area below all other sign headers is white.

Non-Adhesive Pre-Printed & Pre-Cut Safety Tags (B-551)


Pre-printed and pre-cut to save you time!

- Non-adhesive semi rigid card stock
- Tags are pre-cut with hole and chamfered corners
- Perforated between tags
- Snap-in plastic grommets available for extra strength around mounting hole

Service temp: -40°F to 180°F Application temp: 0°F to 180°F
Average Outdoor Durability: 8-10 years



Figure 69



Fits Printer Model(s)	Diagram	Catalog #	Header	Tag Width A Inch (mm)	Tag Height B Inch (mm)	Tags Per Row	Tags Per Roll	Rec. Ribbon
BBP31, BBP33	Fig. 69	B30-255-551-ANSIDA		3.250 (82.6)	5.750 (146.1)	1	100	B30-R10000
BBP31, BBP33	Fig. 69	B30-255-551-OSHADA		3.250 (82.6)	5.750 (146.1)	1	100	B30-R10000
BBP31, BBP33	Fig. 69	B30-255-551-ANSICA		3.250 (82.6)	5.750 (146.1)	1	100	B30-R10000
BBP31, BBP33	Fig. 69	B30-255-551-WHT		3.250 (82.6)	5.750 (146.1)	1	100	B30-R10000