




3D VIEW



P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REVISED PER E.O. P16661	16MAY2000	-	RDR
D		REVISED PER E.O. P20223	14MAY2009	-	RDR
E		REVISED-PER PCN-24-226269	06JAN2025	AJT	MB
E1		REVISED PER PCN-25-253066	25JUN2025	UBF	MB



5 ORIENTATION OF "DEUTSCH" AND "-P016" TO BE OPTIONAL.

4 MATERIAL:CONNECTOR: PA66 GF15, GRAY  
 CAP: PA66, GF15, BLACK  
 WEDGE LOCK (INCLUDED): PBT GF30 (GREEN)  
 PINS:COPPER ALLOY, GOLD PLATED

3 THE 12 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 78 AMPS, 13 AMPS PER PIN.

2. FOR WIRE, CONTACT PERFORMANCE, AND APPLICATION CHARACTERISTICS, SEE ENVELOPE DRAWING 0425-015-0000 AND 0425-017-0000.

1. MATES WITH DT06-12SA-XXXX (XXXX = ALL MODIFICATIONS).CONSULT FACTORY FOR MODIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BURKE 05MAY2000	TE Connectivity				
DIMENSIONS: INCHES [mm]		CHK B. BYFORD 13MAY2009					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. BEARD 13MAY2009	NAME DT 12 WAY RECEPTACLE KEY ARRANGEMENT A 12 PIN BUSBAR-GOLD PLATED COLOR: GREY				
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025[0,63] 4 PLC ± ANGLES ±		PRODUCT SPEC 108-151009	SIZE A3	CAGE CODE 00779	DRAWING NO DT04-12PA-P016	RESTRICTED TO -	
MATERIAL		APPLICATION SPEC 114-151009	WEIGHT 26 g	SCALE 2:1		SHEET 1 OF 1	REV E1
4		CUSTOMER DRAWING					